

Surge protection device - TT-SLKK5-S- 5DC - 2809584


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Modular terminal block with suppressor diode as surge voltage protection between clamping connector and DIN rail, separate ground connection, nominal voltage: 5 V AC, mounting on NS 35/7.5, terminal width: 6.2 mm, terminal height: 69 mm



Key commercial data

Packing unit	50 pc
GTIN	 4 017918 101268
Weight per Piece (excluding packing)	19.24 g
Custom tariff number	85363030
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Height	66.5 mm
Width	6.2 mm
Depth	69.5 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Degree of protection	IP20

General

Housing material	PA
Inflammability class according to UL 94	V2
Color	black
Mounting type	DIN rail: 35 mm
Type	Single-level terminal block – separate PE connection
Direction of action	Line-Earth Ground

Protective circuit

Surge protection device - TT-SLKK5-S- 5DC - 2809584

Technical data

Protective circuit

IEC test classification	C1
	C3
VDE requirement class	C3
Nominal voltage U_N	5 V AC
Maximum continuous voltage U_C (wire-ground)	5.8 V DC
	4 V AC
Nominal current I_N	32 A (50 °C)
Operating effective current I_C at U_C	≤ 2 mA
Residual current I_{PE}	≤ 2 mA
Nominal discharge current I_n (8/20) μ s (Core-Earth)	746 A
Total surge current (8/20) μ s	746 A
Max. discharge current I_{max} (8/20) μ s maximum (Core-Earth)	746 A
Nominal pulse current I_{an} (10/1000) μ s (Core-Earth)	143 A
Output voltage limitation at 1 kV/ μ s (Core-Earth) spike	≤ 12 V
Output voltage limitation at 1 kV/ μ s (Core-Earth) static	≤ 9 V
Residual voltage at I_n , (conductor-ground)	≤ 13.4 V
Response time t_A (Core-Earth)	≤ 1 ns
Cut-off frequency f_g (3 dB), asym. (PE) in 150 Ohm system	typ. 300 kHz
Capacity (Core-Earth)	4.75 nF
Surge protection fault message	None
Impulse durability (conductor-ground)	C1 (500 A/250 A)
	C3 - 100 A

Connection data

Connection method	Screw connection
Connection type IN	Screw terminal blocks
Connection type OUT	Screw terminal blocks
Screw thread	M3
Tightening torque	0.5 Nm
Stripping length	8 mm
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	4 mm ²
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12

Standards and Regulations

Standards/regulations	IEC 61643-21
-----------------------	--------------

Surge protection device - TT-SLKK5-S- 5DC - 2809584

Classifications

eCl@ss

eCl@ss 4.0	27140201
eCl@ss 4.1	27130801
eCl@ss 5.0	27130801
eCl@ss 5.1	27130801
eCl@ss 6.0	27130807
eCl@ss 7.0	27130807
eCl@ss 8.0	27130807

ETIM

ETIM 2.0	EC000943
ETIM 3.0	EC000943
ETIM 4.0	EC000943
ETIM 5.0	EC000943

UNSPSC

UNSPSC 6.01	30212010
UNSPSC 7.0901	39121610
UNSPSC 11	39121610
UNSPSC 12.01	39121610
UNSPSC 13.2	39121620

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC

Accessories

Accessories

Surge protection device - TT-SLKK5-S- 5DC - 2809584

Accessories

End cover

End cover - D-UKK 3/5 BK - 2770228



End cover, Length: 56 mm, Width: 2.5 mm, Height: 66.5 mm, Color: black

Labeled terminal marker

Zack Marker strip, flat - ZBF 6,LGS:FORTL.ZAHLEN - 0808749



Zack Marker strip, flat, Strip, white, labeled, Printed horizontally: Consecutive numbers 1 - 10, 11 - 20, etc. up to 91 - 100, Mounting type: Snap into flat marker groove, for terminal block width: 6.2 mm, Lettering field: 5.15 x 6.15 mm

Marker for terminal blocks - ZB 6,LGS:L1-N,PE - 1051414



Marker for terminal blocks, Strip, white, labeled, can be labeled with: Plotter, Horizontal: L1, L2, L3, N, PE, L1, L2, L3, N, PE, Mounting type: Snap into tall marker groove, for terminal block width: 6.2 mm, Lettering field: 6.15 x 10.5 mm

Marker for terminal blocks - ZB 6,LGS:U-N - 1051430



Marker for terminal blocks, Strip, white, labeled, can be labeled with: Plotter, Printed horizontally: U, V, W, N, GND, U, V, W, N, GND, Mounting type: Snap into tall marker groove, for terminal block width: 6.2 mm, Lettering field: 6.15 x 10.5 mm

Zack marker strip - ZB 6,LGS:FORTL.ZAHLEN - 1051016



Zack marker strip, Strip, white, labeled, can be labeled with: Plotter, Printed horizontally: Consecutive numbers 1 - 10, 11 - 20, etc. up to 491 - 500, Mounting type: Snap into tall marker groove, for terminal block width: 6.2 mm, Lettering field: 6.15 x 10.5 mm

Marker pen

Surge protection device - TT-SLKK5-S- 5DC - 2809584

Accessories

Marker pen - B-STIFT - 1051993



Marker pen, for manual labeling of unprinted Zack strips, smear-proof and waterproof, line thickness 0.5 mm

Partition plate

Spacer plate - DP-UKK 3/5 BK - 2770833



Spacer plate, to compensate for level offsets, Length: 56 mm, Width: 2.5 mm, Height: 25 mm, Color: black

Terminal marking

Zack Marker strip, flat - ZBF 6:UNBEDRUCKT - 0808710



Zack Marker strip, flat, Strip, white, unlabeled, can be labeled with: Plotter, Mounting type: Snap into flat marker groove, for terminal block width: 6.2 mm, Lettering field: 5.15 x 6.15 mm

Zack Marker strip, flat - ZBF 6/WH-100:UNBEDRUCKT - 0808736



Zack Marker strip, flat, Strip, white, unlabeled, can be labeled with: Plotter, Mounting type: Snap into flat marker groove, for terminal block width: 6.2 mm, Lettering field: 5.15 x 6.15 mm

Zack marker strip - ZB 6:UNBEDRUCKT - 1051003



Zack marker strip, Strip, white, unlabeled, can be labeled with: Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 6.2 mm, Lettering field: 6.15 x 10.5 mm

Additional products

Surge protection device - TT-SLKK5-S- 5DC - 2809584

Accessories

End cover - D-UKK 3/5 BK - 2770228



End cover, Length: 56 mm, Width: 2.5 mm, Height: 66.5 mm, Color: black

Spacer plate - DP-UKK 3/5 BK - 2770833



Spacer plate, to compensate for level offsets, Length: 56 mm, Width: 2.5 mm, Height: 25 mm, Color: black

Shield connection - SSA 3-6 - 2839295



shield fast connections for conductor diameter 3 - 6 mm. Potential connection cable: 200 mm, black

Shield connection - SSA 5-10 - 2839512



Shield fast connection for conductor diameters 5 - 10 mm. Potential connection cable: 200 mm, black

Drawings

Circuit diagram

