

Denna ritning är Pressmaster AB:s egendom. Skyddad av gällande lag.
This drawing is the property of Pressmaster AB. Protected in accordance with privailing law.



För icke direkt toleranssatta mått
gäller toleransklass
General tolerances if not other-
wise stated

NOM DIM MM		TOL CLASS		
From	To	A	B	C
(1)	6	±0.05	±0.1	±0.2
(6)	30	±0.1	±0.2	±0.5
(30)	100	±0.15	±0.3	±0.8
(100)	300	±0.2	±0.5	±1.2
(300)	1000	±0.3	±0.8	±2


Hål / Holes H13

Skarpa kanter brutna där ej annat anges.
No sharp edges unless otherwise specified.

Övriga generella toleranser enligt
ritning 4100-4644.
Additional general tolerances in
accordance with drawing 4100-4644.



4101-0273



4300-3766

FÖRSPÄNNING / PRELOAD: 130 ± 20 N		
Tolkmått / Gauge dimensions (mm)		
URTAG	Gåtolk	Stopptolk
NEST	GO	NO GO
2.54	ø2.49	ø2.59
9.75	ø9.70	ø9.80

Material			Behandling/Treatment				Status Frisläppt	
Konstr/Design OS	Ritad/Drawn TGW	Datum/Date 2009-11-03		Skala/Scale 1:2	Kontr/Checked IP	Godk/Approved NE	Ämne/Blank	
pressmaster ISO 9001 REG NR FM13647			Benämning/Denomination KRIMPTÅNG 298-1052 CRIMPING TOOL			Vikt/Weight,gram		Art grp 012
						Ritn nr/Drawing no 43002437		REV 009