76341-329LF - DUBOX™ : 29 Position PCB Mounted Receptacle Through Mount, Top Entry, Single Row

PRE - RELEASED



www.fci.com

Mating Half

77311-101-29LF

Specifications

General	
Hold Down Style	No Locating Pegs
Number of contacts (per row)	29
Number of contacts (Total)	29
Number of rows	1
Orientation	Vertical
Packaging	Tube
Mating half	Mates with 0.64 mm (0.025 in.) Square pins.
Series Number	76341
Dimensional	
Thickness (Board)	1.6 mm (0.062 in.) or 2.36 mm (0.093 in.)
Footprint (Board)	2.54 mm x 2.54 mm (0.1 in. x 0.1 in.)
Electrical	
Current rating	3A max. per Contact/2A max. per Contact for Full Load
Resistance (Contact)	15 milli ohms Initial, 20 milli ohms After test
Resistance (Insulation)	100000 M-ohms
Voltage rating	1000V rms
Mechanical	
Insertion force	1.50N (150 gf) per Contact
Withdrawal Force	0.3N (30 gf) min. per Contact
Mounting	
Solder process	Compatible with Wave Soldering Processes
Physical	
Color (Housing)	Blue
Material (Contact)	Phosphor Bronze
Material (Housing)	Glass - Filled Thermoplastic Polyester
Plating (Contact area)	0.76 µm (30 µin.) Gold

Plating (Tail)	2.54 µm (100 µin.) Tin
Underplating (Contact)	1.27 µm (50 µin.) Nickel
Flammability rating	UL 94 V-0
Temperature (Range)	-65 °C to +125 °C

Approvals / Certifications

UL File Number	E66906
CSA File Number	LR46923
Approvals / Certifications	UL and CSA Approved

PRODUCT NUMBER
76341-YXXXLF

- WHEN NEEDED, SUFFIX LETTER "LF" INDICATES THE PRODUCT IS RoHS COMPATIBLE, SEE NOTE 5.
- OPTIONAL LETTER
  H: HIGH TEMPERATURE PRODUCT.
- NUMBER OF POSITIONS: 02 TO 50.
- PLATING CODE
  3= 0.76µm GOLD ON CONTACT AREA.
  3.81µm TIN-LEAD ON TAIL.
  4= 5µm TIN-LEAD ON CONTACT AREA.
  3.81µm TIN-LEAD ON TAIL.
  WHEN SUFFIX "LF" IS REQUIRED, 2µm MIN MATTE TIN OVER 1.27 MIN Ni IS SUPPLIED INSTEAD OF SnPb.







NOTES:

1 – HOUSING MAT'L: THERMOPLASTIC GLASS FILLED
FLAME RETARDANT PER UL 94 V-0
LOW TEMPERATURE: COLOR BLUE
HIGH TEMPERATURE: COLOR GREY.

2 – TERMINAL MATERIAL: PHOSPHOR BRONZE.

3 – 2 UP TO 4 POSITIONS PRODUCT PACKED IN PLASTIC BOX.
5 UP TO 50 POSITIONS PRODUCT PACKED IN TUBE.

4 – TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS
EXAMPLE: 8 POS: (Nx2.54)-0.08=20.24 mm

5 – RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a – PLATING:
– "LF" MEANS THE PRODUCT IS LEAD-FREE, 2µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.

b – MANUFACTURING PROCESS COMPATIBILITY
– THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C ±5°C SOLDER BATH TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MIN THICK CIRCUIT BOARD.

c – LABELING:
– MEETS PACKAGING SPECS AS PER GS-14-920

d – LEGAL STATEMENT: SEE GS-22-008

6 – END STAND-OFFS FOR 1x2 UP TO 1X5 POS
NO END STAND-OFFS FOR 1x6 UP TO 1x50 POS

ltr	ecn no	dr	date
P	F11-0043	JCO	12.02.22
J	F80115	PNZ	98.01.22
K	F10110	GCO	01.01.16
L	F03-0284	DLE	03.10.07
M	F04-0347	DLE	04.09.27
N	F06-0204	DLE	06.06.20

sheet index	revision	P	B
	sheet	1	2

mat'l. code: SEE NOTES
surface: ISO 1302
tolerance: ISO 406 ISO 1101
tolerances unless otherwise specified: angles ±2°; linear ±0.3
projection
mm
scale 5:1

dr	D LEGRAND	04.09.27
engr	P NIZZI	04.09.27
chr	D LEGRAND	04.09.27
appd	P NZ	04.09.27

product family: DUBOX
title: BtB RECEPT. VERT SR TMT
dwg no: 76341
sheet 1 of 2
size: A3
type: CUSTOMER Drawing

Copyright FCI
FCIconnect.com
form: A3

PDM: Rev:P STATUS:Released Printed: Mar 20, 2012



RECOMMENDED HOLE PATTERN

mat'l. code: SEE SHEET 1				surface ISO 1302	tolerance ISO 406 ISO 1101	projection	product family: DUBOX	
ltr	ecn no	dr	date	tolerances unless otherwise specified			title: BtB RECEPT. VERT SR TMT	
A	F04-0347	DLE	04.09.27	angles ±2°	linear ±0.3	mm		
B	F06-0204	DLE	06.06.20			scale 5:1		
				dr D LEGRAND	04.09.27		dwg no 76341	sheet 2 of 2
				engr P NIZZI	04.09.27			size A4
				chr D LE	04.09.27			
				appd P NZ	04.09.27		type CUSTOMER Drawing	
sheet index	revision sheet							

form: A4

FCIconnect.com
Copyright FCI
PDM: Rev:P
STATUS:Released
Printed: Mar 20, 2012