

Lynx-S

SA LYNX-S 11W/827 G23 SLV 10

0025883



Range features

- Single pin-base compact lamps, suitable for wide range of applications
- Excellent colour rendering - (CRI=85)
- For use with magnetic ballast
- Available in Homelight (2700K), Warm White (3000K) and Cool white (4000K)
- Average rated life: 10000 hours



PRODUCT OVERVIEW

Ordering number	0025883
Technology	Compact Fluorescent
Light colour	827 Homelight
Energy class	A
Average life (Rated) (h)	10000
Lamp shape	Stick
Lamp finish	frosted
Dimmable	NO
Cap/Base	G23
Type	Lynx S
EAN code	5410288258836
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	900
Efficacy (Rated) (lm/w)	76
Watt (Nominal) (W)	11
Voltage (V)	91

Lynx-S

SA LYNX-S 11W/827 G23 SLV 10

0025883

DATA TABLE

General data

Ordering number	0025883
Dry applications use only	yes
Technology	Compact Fluorescent
Average life (Nominal) (h)	10000
Energy class	A
Average life (Rated) (h)	10000
Lamp shape	Stick
Lamp finish	frosted
Dimmable	NO
Cap/Base	G23
Type	Lynx S
EAN code	5410288258836
E-number FI	4944082
E-number SE	8357264
Long description	Single pin-base compact lamps, suitable for wide range of applications. Excellent colour rendering - (CRI=85). For use with magnetic ballast. Available in Homelight (2700K), Warm White (3000K) and Cool white (4000K). Average rated life: 10000 hours
Product name	SA LYNX-S 11W/827 G23 SLV 10
Lamp mercury content (mg)	< 2.50 mg
Starting time (max) (s)	10 Sec
Control gear required	Yes
Fixture rating	Open
IEC Reference	IEC 60901
IEC Reference 2	IEC 61199
IEC Reference 3	IEC 60921
Intended purpose	General lighting
Special purpose lamp	No
Transformer required	No
Sales pack quantity	10
Rated survival factor at 2000 h 50Hz	0.98
Rated survival factor at 4000 h 50Hz	0.9
Rated survival factor at 6000 h 50Hz	0.7
Rated survival factor at 8000 h 50Hz	0.50
Rated survival factor at 12000 h 50Hz	0.62

Lynx-S

SA LYNX-S 11W/827 G23 SLV 10

0025883

Optical data

Light colour	827 Homelight
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	900
Luminous flux (Nominal) (lm)	900
Ambient temperature for maximum luminous flux (°C)	25
Rated lumen maint. factor at 2000 h 50Hz	0.85
Rated lumen maint. factor at 4000 h 50Hz	0.78
Rated lumen maint. factor at 6000 h 50Hz	0.76
Rated lumen maint. factor at 8000 h 50Hz	0.75
Rated lumen maint. factor at 12000 h 50Hz	0.8

Electrical data

kWh per 1000 hours burning time	14
Rated lamp efficacy (lm/W) 100H 50Hz at optimum temp.	76
Efficacy (Rated) (lm/w)	76
Watt (Rated) - High frequency (W)	50
Watt (Rated) (W)	11.8
Watt (Nominal) (W)	11
Voltage (V)	91
Current (A)	0.155

Physical data


Length base to base (mm) - A	236
Lamp Length (mm) - C/L	213
Lamp Diameter (mm) - D	32.5
Packaging outer width (cm)	8.1
Packaging outer length (cm)	12.3
Packaging outer height (cm)	24.9
Packaging single length (cm)	2.3
Packaging single width (cm)	3.6
Packaging single height (cm)	23.7

Lynx-S

SA LYNX-S 11W/827 G23 SLV 10

0025883

TECHNICAL DRAWINGS



ENERGY LABEL

