

D2.5/8.SFLT.2L



Products Low Voltage Products and Systems Connection Devices Terminal Blocks SNA Series

General Information

Extended Product Type:	D2.5/8.SFLT.2L
Product ID:	1SNA290093R2000
EAN:	3472592900933
Catalog Description:	D2.5/8.SFLT.2L Spring Terminal Blocks - For 5 x 20 and 5 x 25 fuses - with blown fuse indicator and test sockets - Grey
Long Description:	- Protect your circuits with 5 x 20 and 5x 25 fuse terminal blocks (fuse not delivered with the terminal blocks), - Quickly identify the defective circuit thanks to the blown fuse indicator, - Easy to access thanks to the front wiring entry, - Clamping contact pressure non dependent on the operator and automatic creeping compensation.

Additional Information

ABB Industrial IT Suite:	Control IT
Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Ambient Temperature:	-5 ... +40 °C
Color:	Grey
Connecting Capacity Main Circuit UL/CSA:	Spring Clamp / Flexible 1x 26 ... 12 AWG Spring Clamp / Rigid 1x 26 ... 12 AWG
Connecting Capacity UL/CSA:	Stranded 12 AWG
Connecting Capacity Main Circuit:	Spring Clamp / Flexible 1x 0.12 ... 2.5 mm ² Spring Clamp / Rigid 1x 0.12 ... 4 mm ² Spring Clamp / With Insulated Ferrule 1x 0.5 ... 1.5 mm ²
Connection Type:	Spring
Country of Origin:	France (FR)
Customs Tariff Number:	85369010
Data Sheet, Technical Information:	1SNC160019C0202
Declaration of Conformity - CE:	1SND225019U1000
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
EAC Certificate:	1SND162001A1100
EAN:	3472592900933
ETIM 4:	EC000899 - Fuse terminal block
ETIM 5:	EC000899 - Fuse terminal block
ETIM 6:	EC000899 - Fuse terminal block
Environmental Information:	1SND220035E1002
Flammability According to UL94:	V0
Function:	Fuse
Gauge Type:	A2
IIT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Instructions and Manuals:	1SNC160019C0202
Insulation Material:	Polyamide
Invoice Description:	D2.5/8.SFLT.2L Spring Terminal Blocks - For 5 x 20 and 5 x 25 fuses - with blown fuse indicator and test sockets - Grey
Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Minimum Order Quantity:	50 piece
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

Number of Connections:	2
Number of Levels:	1
Object Classification Code:	X
Package Level 1 EAN:	3472592900933
Package Level 1 Gross Weight:	0.75 kg
Package Level 1 Height:	75 mm
Package Level 1 Length:	200 mm
Package Level 1 Units:	50 piece
Package Level 1 Width:	176 mm
Package Level 2 Gross Weight:	7.250 kg
Package Level 2 Height:	300 mm
Package Level 2 Length:	500 mm
Package Level 2 Units:	450 piece
Package Level 2 Width:	300 mm
Pollution Degree:	3
Product Main Type:	D2.5/8.SF.2L
Product Name:	Terminal block
Product Net Depth:	45.5 mm
Product Net Height:	80 mm
Product Net Weight:	15 g
Product Net Width:	8 mm
Product Packing Type:	Box
Rated Cross-Section:	2.5 mm ²
Rated Current (I _n):	Main Circuit 6.3 A
Rated Impulse Withstand Voltage (U _{imp}):	8000 V
Rated Voltage (U _r):	630 V
Recommended Screw Driver:	3.5 mm
RoHS Information:	1SND230488F0201
RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q4
Selling Unit of Measure:	piece
Short Description:	Spring Terminal Blocks D2.5/8.SFLT.2L
Spacing:	8 mm
Sub-Function:	for 5x20 and 5x25 Fuses
Sub-Function 3:	For 5x20 and 5x25 Fuses
Sub-Function 4:	With blown fuse indicator Neon
Wire Stripping Length:	9.5 mm
cUL Certificate:	1SND162000A0204

