


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION, 19
© COPYRIGHT — BY —

2		1		LOC	AF	DIST	50
REVISIONS							
P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED	
			R1	REVISED PER ECO-11-005294	08APR11	HMR	



- DIMENSIONS IN BRACKETS ARE IN INCHES
2-CONTINUOUS STRIP ON REELS

TIN	[.016] 0.41 STL.	[.090-.130] 2.29-3.30	[22-18] 0.3-0.8mm ²	[.032] 0.81	42510-4
NICKEL	[.016] 0.41 STL.	[.090-.130] 2.29-3.30	[22-18] 0.3-0.8mm ²	[.032] 0.81	42510-3
TIN	[.016] 0.41 BR.	[.090-.130] 2.29-3.30	[22-18] 0.3-0.8mm ²	[.032] 0.81	42510-2
NONE	[.016] 0.41 BR.	[.090-.130] 2.29-3.30	[22-18] 0.3-0.8mm ²	[.032] 0.81	42510-1
FINISH	MATERIAL	INSULATION RANGE	WIRE SIZE	TAB THK [1.001] 0.025	PART NO.

METRIC

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. M.M. TOLERANCES ON: DECIMALS ±.015 ANGLES ±	CONTRACT NO. BR <i>NR Rutt</i> 10/28/83 CHK <i>G. Yeller</i> 11/3/83 APPD <i>C. Meyers</i> 11-7-83 APPD <i>V. K...</i> 11-16-83 DSGN APPD OTHER APPD	NAME 250 SERIES FASTON RECEPTACLE
SEE ABOVE	SIZE B	FSCM NO 00779
FINISH SEE ABOVE	SCALE	DRAWING NO 42510
		SHEET