

ZEICHNUNG GESCHÜTZT DURCH
©COPYRIGHT 1988
AMP DEUTSCHLAND GMBH
ALLE RECHTE VORBEHALTEN


REV.	ÄNDERUNG	DATUM	NAME
1	MASS 2.54 ± 0.3 WAR 2.54		
	MASS 3.0 ± 0.2 WAR 3.0 HINZU ALLG. TOLERANZ ± 0.1	02.11.88	AUGUSTINIAK
2	ZEICHNUNG IN EUROPEAN PROJECTION GEÄNDERT	04.12.90	A.HO
3	LÖTLÄNGE VON 3 IN 3.1 GEÄNDERT	12.03.92	A.HO
C	VERPACKUNGSANGABE HINZU	15.01.96	F.RDT

DO NOT SCALE

DIMENSIONS IN mm





METRIC

EUROPEAN
PROJECTION



NOTES:

- TO DETERMINE DIMENSIONS TAKE $2 \times N = \text{NR. OF POS.}$
FOR EXAMPLE: $2 \times 10 \text{ POS.} : N \times 2.54 = 25.4 \text{ mm.}$
FOR ORDERNR. USE BASIC NR. + NR. OF POS.
FOR EXAMPLE: $2 \times 2 \text{ POS.} = 215 \text{ 307-2 (SHORTEST VERSION)}$
 $2 \times 36 \text{ POS.} = 3-215 \text{ 307-6 (LONGEST VERSION)}$
- HOUSING MATERIAL: GREEN GLASSFILLED POLYESTER,
UL 94V-0
CONTACT MATERIAL: PHOSPHORBRONZE.
- PLATING: UNDERCOATING: $1.3 \mu\text{m Ni.}$
AT CONT. PLACE: $0.8 \mu\text{m Au.}$
AT SOLDER-TYNES: $2.5 \mu\text{m Sn.Pb.}$
- MATES WITH 0.63 SQUARE/ROUND MODU POSTS.
- CONTACT-POINT.
- RECOMMENDED P.C. BOARD-THICKNESS: 1.6.
- RETENTION FEATURE.
- HV100 CONNECTOR PACKED IN ANTISTATIC BLISTER



P.C.-BOARD HOLE-PATTERN

NICHT TOLERIERTE MASSE
$\pm 0.1 \text{ mm}$
$\pm -$
MASSTAB 5:1

VERWENDET FÜR E 91-52 572		SEE NOTES FINISH	SEE NOTES MATERIAL	SEE NOTES PARTNUMBER
CUSTOMER DRAWING		AMP		
FOR REFERENCE ONLY WILL NOT BE UPDATED		AMP-HOLLAND B.V. 's-Hertogenbosch, The Netherlands.		
DR. R.VISSER		THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION 8.5.1987		
DATE 08.05.87		© COPYRIGHT 1987 BY AMP-HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.		
CHK. W.SIMONS		WIRE RANGE -	NAME HV 100 VERTICAL CONNECTOR	
DATE		INSUL. RANGE -	DUAL ROW, 7.0mm HEIGHT, TOP ENTRY, GOLD, MAX. 2x36 POSITIONS.	
APP. L.v. SOEST		SIZE A3	SHEET 1 OF 1	REV. DATE D M Y 150196
DATE		DWG. No. 215307		REV. LTR. C

8 7 6 5 4 3 2 1