



## Combination spanner, offset, 1952Z

Combination spanner, offset in Inch sizes  
DIN 3113 / ISO 3318 / ISO 7738






**Finish:** nickel and chrome-plated, sizes up to 1 1/2" fine-polished.

**Material:** VANADIUM-EXTRA.

Open-end angle 15°, ring end 10° offset, equal openings at both ends.

With Dynamic-Drive-Profile up to 1 1/2".



				L mm	a2xa1 mm	b2xb1 mm	
1952Z-1/4	1057480	5	1/4	95	4.5x3.7	9.5x14.0	15
1952Z-5/16	1057497	5	5/16	115	5.5x4.2	12.2x18.0	23
1952Z-11/32	0111046	5	11/32	125	6.0x4.5	13.2x20.0	30
1952Z-3/8	1057503	5	3/8	125	6.0x4.5	13.2x20.0	30
1952Z-7/16	1057510	5	7/16	145	7.0x5.0	16.2x24.0	49
1952Z-1/2	1057527	5	1/2	170	8.0x5.6	19.0x28.5	68
1952Z-9/16	1057534	5	9/16	185	8.5x6.0	20.5x31.0	80
1952Z-5/8	1057541	5	5/8	205	9.8x6.5	23.5x35.0	110
1952Z-11/16	1057558	5	11/16	220	10.6x7.0	24.5x37.0	135
1952Z-3/4	1057565	5	3/4	245	12.2x7.5	27.0x41.5	195
1952Z-13/16	1057572	5	13/16	265	13.0x8.0	28.5x43.5	217
1952Z-7/8	1057589	5	7/8	265	13.5x8.5	32.0x48.0	305
1952Z-15/16	1057596	5	15/16	300	14.5x9.0	34.5x52.0	375
1952Z-1	1057602	1	1	330	15.5x9.5	36.0x54.5	400
1952Z-1.1/16	1057619	1	1 1/16	330	16.5x10.0	38.5x59.0	590
1952Z-1.1/8	1057626	1	1 1/8	370	17.0x10.0	40.0x61.0	700
1952Z-1.1/4	1057633	1	1 1/4	390	19.0x11.5	45.5x68.0	745
1952Z-1.5/16	1057718	1	1 5/16	415	20.0x12.0	48.0x72.0	800
1952Z-1.3/8	1057732	1	1 3/8	415	20.0x12.0	48.0x72.0	800
1952Z-1.7/16	1057749	1	1 7/16	435	21.0x13.5	52.0x78.0	990
1952Z-1.1/2	1057756	1	1 1/2	435	21.0x13.5	52.0x78.0	990
1952Z-1.5/8	1057763	1	1 5/8	495	24.4x14.4	61.5x86.7	1350