



GE  
Lighting



## Candle

TU 30W HALO C/CL/E14 240V GE TWBX  
2/20TR

# 98367

---

### Product information

GE's HaloCandle range is a direct replacement for regular incandescent lamps offering a crisp white light. These bulbs are the environmentally friendly solution for those who prefer the features and light quality associated with incandescent bulbs.

- Last twice as long and consume up to 30% less electricity than corresponding incandescent lamps.
- Provide instant-on, full light output at start-up and lumens are maintained throughout the life of the product.
- Unlike some compact fluorescent products, these lamps are 100% retrofit with the incandescent lamps they replace.
- Can be used with dimming switches.
- Environmentally friendly with no lead or mercury.
- Up to 2,000 hours life
- Excellent colour rendering, light close to natural (100% CRI)

- More than 90% lumen maintenance over life
-

## Product data

Cap/Base	E14
Bulb Shape	Candle
Bulb Diameter [mm]	35
Dimming Capability	Yes
Maximum Overall Length [mm]	99.5
DUN Code	10043168983676
EAN Code	0043168983679
Net weight per piece [g]	18
Gross weight per piece [g]	25
Brand	General Electric (GE)

## Performance data

Nominal power [W]	30
Nominal lamp voltage [V]	240
Nominal lumens [lm]	405
Colour temperature [K]	2800
Colour Rendering Index (CRI) [Ra]	100
Rated Life [h]	1000
Energy efficiency class (EEC)	D
Weighted energy consumption [kWh/1000h]	31.53

## Logistic data

Pack Quantity	20
Inner pack type	TWIN BOX
Outer pack type	TRAY OUTER
Layer quantity	600 EUR, 760 UK
Layer quantity EUR	600
Layer quantity UK	760
Pallet quantity EUR (PC)	6000
Pallet quantity UK (PC)	7600
Outer case size	180 x 150 x 100 (mm)
Product status	Available while stock lasts

## Application areas



## Downloads & Links

[Go to the catalog site \(HTTP\)](#)

[Halogen Lamps Spectrum Catalogue \(PDF\)](#)

[GLS, Candle, Spherical Lamps Data sheet \(PDF\)](#)

[Lighting design tools & calculators \(HTTP\)](#)

## Disclaimer

Please note that the rated life of those lamps under this SKU number placed on the market on or before 31 August 2013 can be either 1,000 hours or 2,000 hours. The rated life of those lamps placed on the market on or after 1 September 2013 is exclusively 2,000 hours.