

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [43879-0022](#)  
**Status:** **Active**  
**Overview:** [Mini-Fit® Blind Mate Interface \(BMI\) Connectors](#)  
**Description:** Mini-Fit® BMI Header Compliant Pin Interface, Dual Row, Vertical, 4 Circuits, Tin (Sn) Plating

**Documents:**

<a href="#">3D Model</a>	<a href="#">Test Summary TS-43879-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-43879-001 (PDF)</a>	<a href="#">Product Literature (PDF)</a>

**Agency Certification**

CSA	LR19980
TUV	R72081037
UL	E29179

**General**

Product Family	PCB Headers
Series	<a href="#">43879</a>
Application	Board-to-Board, Power, Wire-to-Board
Application Tooling Part Link	62200-5800
Application Tooling Part Link	62200-9400
Comments	Square Pin Compliant Pin
Overview	<a href="#">Mini-Fit® Blind Mate Interface (BMI) Connectors</a>
Product Literature Order No	USA-143
Product Name	Mini-Fit® BMI
UPC	800753952096

**Physical**

Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass, Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	2.949/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	6.35mm
PCB Locator	No
PCB Retention	Yes
Packaging Type	Tray
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes



**EU RoHS**

**ELV and RoHS Compliant**

**REACH SVHC Contains SVHC: No Low-Halogen Status Not Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[43879Series](#)

**Mates With**

[15-06-0040](#) UL 94V2 Mini-Fit® BMI Receptacle Housing, [15-06-0041](#) UL 94V0 Mini-Fit® BMI Receptacle Housing, [15-24-7040](#) UL 94V2 Mini-Fit® BMI Receptacle Header, [15-24-7041](#) UL 94V0 Mini-Fit® BMI Receptacle Header

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Flat Rock Tool for Header	<a href="#">0622009400</a>
Compliant Pin Insertion Tooling Kit for Arbor Press	<a href="#">0622005800</a>

Polarized to PCB	No
Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Through Hole - Compliant Pin

**Electrical**

Current - Maximum per Contact	8A
Voltage - Maximum	600V

**Material Info****Reference - Drawing Numbers**

Product Specification	PS-43879-001
Sales Drawing	SD-43879-021
Test Summary	TS-43879-001

This document was generated on 08/26/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**