

Markers for sticking on, screwing or riveting - US-EMLSP (28X10) YE - 0830344

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Markers for sticking on, screwing or riveting, Card, yellow, unlabeled, can be labeled with: THERMOMARK CARD, Mounting type: Screws, rivets, Adhesive, Lettering field: 28 x 10 mm




The figure shows a version of the article

Why buy this product

- The stick-on UniSheet markers can also be attached with screws or rivets
- The markers, which are supplied in uniform sheets, can be marked quickly, easily, and inexpensively using the THERMOMARK CARD
- The perforated markers are easy to separate and can be easily fitted



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 708210
Weight per Piece (excluding packing)	18.74 g
Custom tariff number	39199000
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	28 mm
Height	0.5 mm
Width (a)	10 mm

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Ambient temperature (assembly)	15 °C ... 25 °C

General

Markers for sticking on, screwing or riveting - US-EMLSP (28X10) YE - 0830344

Technical data

General

Color	yellow
Components	Silicone-free
Inflammability class according to UL 94	V0
Material	PVC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	26
Number of individual labels per row	2
RoHS compliant	Yes
Adhesive	Acrylic
Printability	Thermal transfer
Device	5146464 THERMOMARK CARD
	5146451 THERMOMARK CARD-US-MAG1
Ink ribbon	0801371 THERMOMARK-RIBBON 110-TC
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	IEC 61010-1:2010-06
Result	Test passed
Burning behaviour	self-extinguishing
Foil strength	500 µm
Adhesive strength	50 µm
Marking mounting type	Screws, rivets

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137

Markers for sticking on, screwing or riveting - US-EMLSP (28X10) YE - 0830344

Classifications

eCl@ss

eCl@ss 8.0	27141137
------------	----------

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Accessories

Accessories

Magazine

Magazine - THERMOMARK CARD-US-MAG1 - 5146451



Magazine for the THERMOMARK CARD printer, for accommodating US cards