

## PC-RG6-2

ABB contact for United  
Kingdom

### General Information

---

<b>Extended Product Type:</b>	PC-RG6-2
<b>Product ID:</b>	1SNA519104R0200
<b>EAN:</b>	3472599857636
<b>Catalog Description:</b>	PC-RG6-2 Lateral Jumper Bar - 2 poles - Orange
<b>Long Description:</b>	PC-RG6-2 Ring lug Lateral Jumper Bar - 2 poles

---

### Categories

---

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Lateral Jumper Bars

---

### Ordering

---

<b>EAN:</b>	3472599857636
<b>Minimum Order Quantity:</b>	25 piece
<b>Customs Tariff Number:</b>	85369010

---

### Dimensions

---

<b>Product Net Width:</b>	3.1 mm
<b>Product Net Height:</b>	16.6 mm
<b>Product Net Length:</b>	26.7 mm
<b>Product Net Depth:</b>	26.7 mm
<b>Product Net Weight:</b>	3.74 g

---

### Container Information

---

<b>Package Level 1 Units:</b>	25 piece
<b>Package Level 1 Width:</b>	65 mm
<b>Package Level 1 Height:</b>	31 mm
<b>Package Level 1 Length:</b>	55 mm
<b>Package Level 1 Gross Weight:</b>	0.10000 kg
<b>Package Level 1 EAN:</b>	3472599857636
<b>Package Level 2 Units:</b>	3500 piece
<b>Package Level 2 Width:</b>	230 mm
<b>Package Level 2 Height:</b>	230 mm
<b>Package Level 2 Length:</b>	350 mm
<b>Package Level 3 Units:</b>	112000 piece

---

### Environmental

---

<b>Ambient Air Temperature:</b>	Operation -40...+100 °C Storage -40...+100 °C
---------------------------------	--

---

### Technical UL/CSA

---

<b>Maximum Operating Voltage UL/CSA:</b>	Main Circuit 600 V
<b>Flammability According to UL94:</b>	V2

---

### Additional Information

---

<b>Ambient Temperature:</b>	-25...+70 °C
<b>Color:</b>	Orange
<b>Function:</b>	Jumper Bars
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Insulation Material:</b>	Polyamide
<b>Product Main Type:</b>	PC-RG6
<b>Product Name:</b>	Terminal Blocks Accessories

<b>Rated Current (I<sub>n</sub>):</b>	Main Circuit 41 A
<b>Rated Voltage (U<sub>r</sub>):</b>	800 V
<b>RoHS Date:</b>	20110721
<b>Spacing:</b>	11 mm

---

### **Certificates and Declarations (Document Number)**

---

<b>Declaration of Conformity - CE:</b>	1SND225158C1000
<b>RoHS Information:</b>	1SND230547F0200

---

### **Classifications**

---

<b>ETIM 4.0:</b>	EC000489 - Cross-connector for terminal block
<b>ETIM 5.0:</b>	EC000489 - Cross-connector for terminal block

---

