


Ordering number C12763_FLARE-MINI-A

Family	Flare	FWHM	15+87 degrees
Type	Lens	Efficiency	95 %
LED	NCSxx19A	cd/lm	1.500
Color	Clear	Gerber File	Available
Diameter	16 mm		
Height	8.6 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Glue		
Status	Ready		


Ordering number C12837_FLARE-MINI-A-PIN

Family	Flare	FWHM	15+87 degrees
Type	Lens	Efficiency	95 %
LED	NCSxx19A	cd/lm	1.500
Color	Clear	Gerber File	Available
Diameter	16 mm		
Height	8.6 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, glue		
Status	Ready		


Ordering number CA12764_FLARE-MINI-A

Family	Flare	FWHM	20+112 degrees
Type	Assembly	Efficiency	94 %
LED	NCSxx19A	cd/lm	0.900
Color	Clear	Gerber File	Available
Diameter	16 mm		
Height	9.1 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Tape		
Status	Ready		




Ordering number CA12838_FLARE-MINI-A-PIN

Family	Flare	FWHM	20+112 degrees
Type	Assembly	Efficiency	94 %
LED	NCSxx19A	cd/lm	0.900
Color	Clear	Gerber File	Available
Diameter	16 mm		
Height	9.1 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, tape		
Status	Ready		

Ordering number CA10932
Description 1

Family	Flare	FWHM	9+88 degrees
Type	Assembly	Efficiency	94 %
LED	NCSxx19A	cd/lm	-
Color	Clear	Gerber File	Available
Diameter	29 x 22.8 mm		
Height	12.84 mm		
Style	Rectang		
Optic Material	PMMA		
Holder Material	-		
Fastening	-		
Status	Ready		

NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.



PRODUCT DATASHEET

Flare series

last update 16/11/2012



GENERAL INFORMATION


- Product series especially designed & optimized for NCSxx19A series of LEDs.
- Special care taken to make light distribution as uniform as possible.
- Lens material optical grade PMMA with high UV and temperature resistance. Allows use of high current and temperature conditions.

Please find more information about used material from below:


http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20UL94_Yellow%20Card.pdf

<http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20PLEXIGLAS-Datasheet.pdf>


Luminaire: LEDIL OY C12763 & C12837_FLARE-MINI-A (NCS19) Efficiency=95%
Lamps: 1 x Nichia NCS19 (95lm@250mA)




Luminaire: LEDIL OY C12763 & C12837_FLARE-MINI-A (NCS19) Efficiency=95%
Lamps: 1 x Nichia NCS19 (95lm@250mA)




Luminaire: Ledil Oy CA12764&CA12838_FLARE-MINI-A (Nichia NCS19 95lm @ 250mA) Efficiency=94%
Lamps: 1 x Nichia NCS19 95lm @ 250mA



Luminaire: Ledil Oy CA12764&CA12838_FLARE-MINI-A (Nichia NCS19 95lm @ 250mA) Efficiency=94%
Lamps: 1 x Nichia NCS19 95lm @ 250mA



Luminaire: LEDIL OY C12763 & C12837_FLARE-MINI-A (NCS19) Efficiency=95%
Lamps: 1 x Nichia NCS19 (95lm@250mA)




cd/klm

— C0 - C180


— C90 - C270

Luminaire: LEDIL OY C12763 & C12837_FLARE-MINI-A (NCS19) Efficiency=95%
Lamps: 1 x Nichia NCS19 (95lm@250mA)



cd/klm
— C0 - C180 — C90 - C270


Luminaire: Ledil Oy CA12764&CA12838_FLARE-MINI-A (Nichia NCS19 95lm @ 250mA) Efficiency=94%
Lamps: 1 x Nichia NCS19 95lm @ 250mA



cd/klm

— C0 - C180 — C90 - C270

Luminaire: Ledil Oy CA12764&CA12838_FLARE-MINI-A (Nichia NCS19 95lm @ 250mA) Efficiency=94%
Lamps: 1 x Nichia NCS19 95lm @ 250mA



cd/klm

— C0 - C180 — C90 - C270