


© 1967 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP
PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.



FOR .102 TO .214 WIRE INSULATION DIA.
TONGUE MATERIAL THK. = .040 $\pm$.002

REVISIONS

ZONE	LTR	DESCRIPTION	DATE	APPROVED
B		REDRAWN & REV. P-6077 SK	7-30-69	FCY
C		REVISED PC-5579 WM	10-8-70	me
D		REVISED PC-5578 TC	2-23-77	L.D.
E		REV/0610-0094-98	2-4-99	ME/JS
E1		REV PER ECR 05-013140	10/20/05	KE/TM

1	WIRE TERMINAL	50846	BODY: COPPER (ASTM B152) NICKEL PLATE (QQ-N-290) .0003 AVG EXT. THK.	
			SLEEVE: COPPER (ASTM B152) NICKEL PL (QQ-N-290).00003 AVG. EXT. THK.	
			INSULATION: TEFLON (ASTM D3295) COLOR: BLACK	
QTY	DESCRIPTION	PART NO.	MATERIAL & FINISH	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON: DECIMALS $\pm$.008 ANGLES $\pm$ 5°		CONTRACT NO. 11	AMP INCORPORATED HARRISBURG, PENNSYLVANIA	
MATERIAL SEE TABLE		DR. <i>Steve Kautz</i> 7-29-69	NAME	
		CHK. <i>F.L. [unclear]</i> 7-30-69	WIRE TERMINAL	
		APPD. <i>Twidbel</i> 8-6-69	PIDG TM STRATO-THERM-RING TONGUE	
		REL. <i>Am Ensign</i> 8-6-69	WIRE SIZE: 12-10	
		DSGN APPD.	SIZE B	CODE IDENT NO. 00779
OTHER APPD.		SCALE NTS	SHEET 10F1	