

MR16 Home

MR16 Home 20W 36° 12V GU5.3 SV1

0022584

Range features



PRODUCT OVERVIEW

Light colour	829 Warm w hite
Technology	Halogen
Ordering number	0022584
Average life (Rated) (h)	2000
Energy class	B
Lamp shape	Reflector
Lamp finish	Dichroic
Dimmable	Yes
Cap/Base	GU5.3
Type	MR16
EAN code	5410288225845
CRI (Ra)	100
Beam angle(°)	36
Beam angle(°)	36
Colour temperature (K)	2900
Useful luminous flux (Rated) (lm)	210
Watt (Nominal) (W)	20
Equivalent watt (W)	No
Voltage (V)	12

MR16 Home

MR16 Home 20W 36° 12V GU5.3 SV1

0022584

DATA TABLE

General data

Ordering number	0022584
Technology	Halogen
Average life (Rated) (h)	2000
Average life (Nominal) (h)	2000
Energy class	B
Energy saving lamp	No
Lamp finish	Dichroic
Lamp shape	Reflector
Dimmable	Yes
Cap/Base	GU5.3
Type	MR16
EAN code	5410288225845
Product name	MR16 Home 20W 36° 12V GU5.3 SV1
Lamp mercury content (mg)	0
Starting time (max) (s)	0
Warm-up time to 60% of full light (max) (s)	Instant Full Light
Control gear required	Yes
Control gear availability	Yes
Fixture rating	Open
IEC Reference	IEC 60357
IEC Reference 2	IEC 60432-3
IEC Reference 3	IEC 60630
Intended purpose	General lighting
No. of switching cycles before premature failure (min)	> 8000
Special purpose lamp	No
Transformer required	Yes

Optical data

Light colour	829 Warm w hite
CRI (Ra)	100
Suitable for accent lighting	Yes
Beam angle(°)	36
Beam angle(°)	36
Colour temperature (K)	2900
Useful luminous flux (Rated) (lm)	210
Lumen maintenance at end of nominal life (%)	80
Luminous flux (Nominal) (lm)	210
Peak intensity (cd)	700

MR16 Home

MR16 Home 20W 36° 12V GU5.3 SV1

0022584

Electrical data

kWh per 1000 hours burning time	22
Watt (Rated) (W)	20
Watt (Nominal) (W)	20
Equivalent watt (W)	No
Voltage (V)	12
Lamp power factor	1

Physical data

Lamp Length (mm) - C/L	45
Max. Lamp Diameter (mm) - D	50
Lamp dimension equal to filament lamp equivalent	Yes
Reflector material	Dichroic
Designed for optimum use in non standard conditions	No