

# WCP Outdoor Call Point Range

## Double Pole Changeover Contact Model (Colour Versions)



### > Product Benefits

- Sealed to IP67
- Unique 'Plug & Play' installation concept
- Total 'Flex-Ability' in the choice of operating element
- Anti-Tamper facility
- Enhanced aesthetics and compact design



### Product Overview

Installation efficiency, flexibility and full compliance with the latest standards are at the heart of the new WCP Outdoor Call Point range.


The outdoor WCP is an IP67 sealed manual call point product. The enhanced environmental protection allows the unit to be installed in many external environments where water and dirt are likely to be present, making it a true waterproof and outdoor product.

Installation time and ultimately cost, are of paramount importance to any fire or security installer. The WCP range directly reflects this need by providing a unique 'plug and play' concept designed specifically to reduce installation time. All new WCP products utilise a special terminal block, where all initial installation cabling is terminated. This terminal block is then simply connected to the back of the WCP. Simple, but effective with no re-termination required and no time wasted. In addition, all WCP products are supplied with three standard 20mm knock outs for cable entries, accommodating all types of surface wiring installations.

Both break glass and re-settable operating elements can now be used within a manual call point. To provide you with the greatest 'flex-ability', the new WCP range can be configured as either a break glass or re-settable unit by simply changing from one element to another. No other additional parts or alternative products need to be ordered.

All WCP Outdoor Call Point products also help preserve the integrity of the overall system as illegal removal of the product lid will result in the call point operating and the system going in to alarm.


The WCP4A product version is supplied with a double pole changeover set of contacts. The product utilises two terminal blocks and wiring to the relevant terminals on these terminal connector blocks provides either a 'normally open' or 'normally closed' operation (see wiring diagram overleaf).



## Electrical Specification

Connection Details: See Figure .1  
 Cable Termination: 0.5-2.5mm<sup>2</sup>  
 Maximum Voltage: 30VDC  
 Switch Rating: 2 Amps

Figure .1




## Environmental Specification

Humidity: 0-95% non-condensing  
 Operating Temperature: -30°C to +70°C  
 Storage Temperature: -30°C to +70°C  
 Ingress Protection (IP) Rating: IP67

## Mechanical Specification

Material: PC/ABS  
 Weight: 240g  
 Colours: Green,  
 White,  
 Yellow,  
 Blue.



## Ordering Information

Model	Electrical Configuration	Colour	Mounting	Operating Element	Markings
Non-Stock					
WCP4A-G000SG-11	N/O & N/C Contacts 30VDC	Green	Surface	Glass	Plain
WCP4A-G000SG-12	N/O & N/C Contacts 30VDC	Green	Surface	Glass	EDR
WCP4A-W000SG-11	N/O & N/C Contacts 30VDC	White	Surface	Glass	Plain
WCP4A-Y000SG-11	N/O & N/C Contacts 30VDC	Yellow	Surface	Glass	Plain
WCP4A-B000SG-11	N/O & N/C Contacts 30VDC	Blue	Surface	Glass	Plain
Stock					
WCP4A-G000SF-11	N/O & N/C Contacts 30VDC	Green	Surface	Flexi	Plain
WCP4A-G000SF-12	N/O & N/C Contacts 30VDC	Green	Surface	Flexi	EDR
WCP4A-W000SF-11	N/O & N/C Contacts 30VDC	White	Surface	Flexi	Plain
WCP4A-Y000SF-11	N/O & N/C Contacts 30VDC	Yellow	Surface	Flexi	Plain
WCP4A-B000SF-11	N/O & N/C Contacts 30VDC	Blue	Surface	Flexi	Plain

N/O = Normally Open Contact  
 N/C = Normally Closed Contact

### Accessories

Code	Description
SC070	Pack Of Ten Test Keys
KG1 x 5	Pack Of Five Glass Elements
PS210	Flexible Operating Element
PS200	Plain Hinged Cover
SC071	Pack Of Ten Terminal Blocks

### > KAC Alarm Company Ltd

KAC House, Thornhill Road,  
 North Moons Moat, Redditch,  
 B98 9ND, United Kingdom  
 Tel: +44 (0) 1527 406655  
 Fax: +44 (0) 1527 406677  
 e-mail: marketing@kac.co.uk