

3M™ Heavy Wall Heat Shrink Tubing ITCSN

Data Sheet

June 2011

Description

3M™ Heavy Wall Heat Shrink Tubing ITCSN is designed to provide reliable performance for electrical splices, connections, and terminations, as well as mechanical and environmental protection. This tubing is fabricated from cross-linked polyolefin. The tubing is highly split-resistant and fast-shrinking to provide rapid installation. It comes standard with a factory-applied adhesive/sealant.

Agency Approvals & Self Certifications

UL Listed, UL 486D Standard, File E102356

CSA Certification, File LR86335

Voltage Rating 600 V

Direct burial and Submersible

For use with Listed, Crimp-type, Splice Connectors

All other product claims are made by 3M and not covered by the UL Listing



Features

- Fast and easy installation
- Thick wall top resists puncture and abrasion damage
- Rugged environmental protection
- Versatile, a minimum number of sizes cover the entire range of applications
- Shrink ratio as high as 4:1
- Resists acids and alkalies
- Bonds to a wide variety of substrates
- Reliable and proven
- UV resistant

Applications

- Primary electrical insulation for solid dielectric wire and cable rated to 1000 volts
- For indoor, outdoor or overhead use
- Direct buried or submersible
- Insulating secondary splices
- Physical protection and moisture sealing of high voltage air insulated connectors and lugs, such as lug connections to bus bars
- Relocation of service
- Dig-in repairs
- Sheath repairs

3M™ Heavy Wall Heat Shrink Tubing ITCSN

Standard Sizes and Dimensions

Product Number	Cable Range Size	Minimum Expanded/ Maximum Recovered I.D.	Cable O.D. Use Range Maximum - Minimum	Certification and Listings
	in. (mm)	in. (mm)	in. (mm)	 
ITCSN-400	12-6 AWG (4-10 mm ²)	0.40 / 0.15" (10,2 / 3,8mm)	0.35-0.17" (9 - 3,3 mm)	E102356 LR86335
ITCSN-800	8 -1/0 AWG (10 - 15 mm ²)	0.80 / 0.20" (20,3 / 5,1 mm)	0.65 – 0.24" (18 - 5,6 mm)	E102356 LR86335
ITCSN-01100	2 - 4/0 AWG (35 - 95 mm ²)	1.10 / 0.37" (27,9 / 9,4 mm)	0.88 – 0.40" (24 - 9,4 mm)	E102356 LR86335
ITCSN-1500	3/0 AWG–400 kcmil (95 -185 mm ²)	1.50 / 0.50" (38,1 / 12,7 mm)	1.19 – 0.60" (33 - 12,1 mm)	E102356 LR86335
ITCSN-2000	250 – 750 kcmil (150 - 300 mm ²)	2.00 / 0.65" (50,8 / 16,5 mm)	1.60 – 0.75" (44, - 19,0 mm)	E102356 LR86335
ITCSN-3000	600–1250 kcmil (400 - 625 mm ²)	3.00 / 1.00" (76,2 / 25,4 mm)	2.25 – 1.20" (63,5 - 25,4 mm)	LR86335
ITCSN-4500	1500-2500 kcmil (800 - 1000mm ²)	4.50 / 1.50" (114,3 / 38,1 mm)	4.00 – 1.50" (101,6 - 38,1 mm)	
ITCSN-6000	2.1 – 4.8" (53 - 122 mm ²)	6.00 / 1.80" (152,4 / 45,7 mm)	5.50 – 1.80" (139,7 - 45,7 mm)	

Typical Properties

Not for specifications. Values are typical, not to be considered minimum or maximum. Properties measured at room temperature 73°F (23°C) unless otherwise stated.

Physical Property (Test Method)	Typical Value US units (metric)
Color	Black
Ultimate Tensile Strength (ASTM D412)	2400 PSI (16 Mpa)
Ultimate Elongation	475%
Longitudinal Change	+1, -10%
Secant Modulus (2%) (ASTM D882A)	14,000 PSI (98 Mpa)
Shore D Hardness (ASTM D-2240)	42
Air-Oven Aging [7 days @ 175°F (175°C)] Tensile Strength Elongation	2,680 psi (18 Mpa) 375%
Heat shock (outer wall only) 4 hrs @ 491°F (255 °C)	No dripping, flowing, cracking
Low Temperature Flexibility 4 hrs @ -67°F (-55°C)	No cracking
Specific Gravity (ASTM D792 A-1)	1.28
Continuous Operating Temperature (less adhesive)	110°F-230°F (-55°C-110°C)

Electrical Property	Typical Value US units (metric)
Dielectric Strength (60 mils) (ASTM 149)	500 V/mil
Volume Resistivity (ASTM D257)	1 x 10 ¹⁴ ohm/cm

Chemical Property	Typical Value US units (metric)
Corrosivity (Mil-I-23053/15)	Non-corrosive
Fungus Resistance (ASTM G-21)	Non-nutrient
Water Absorption (ASTM D-570 6.1)	0.05%
Fluid Resistance JR4 Skydrol 600 Solution Gasoline Hydraulic Fluid	>1500 PSI @ V/mil @ 600 V/mil

3M™ Heavy Wall Heat Shrink Tubing ITCSN

Product Selection

Selecting 3M™ Heavy Wall Heat Shrink Tubing ITCSN is easy and straightforward. The largest tubing size that provides a tight fit when fully recovered will produce the maximum wall thickness. Final wall thickness is proportional to the degree of tubing recovery.

Listed Catalogue Number	Wire Size
ITCSN-0400	12 - 6
ITCSN-0800	8 - 1/0
ITCSN-1100	2 - 4/0
ITCSN-1500	250 - 750
ITCSN-2000	250 - 750

Specifications

The heat shrink tubing must be chemically cross-linked, thermally stabilized polyolefin, capable of operation at cable emergency overload temperatures of 266°F (130°C). The tubing must have UL Listing (UL 486D, 600V) and be approved for the use and be CSA Certified. Supplied tubing lengths of 4 feet and less shall be adhesive lined. The minimum shrink temperature shall be 250°F (121°C).

Engineering/ Architectural Specifications

The tubing must be usable in both indoors and outdoors, in overhead, direct-buried, or submerged applications on cables rated up to 1000 volts. It is resistant to moisture, mild acids and alkalies, fuels, oils, ozone, or ultraviolet light. It is compatible with and adheres to most types of cable jackets, including rubber, plastic or lead.

Performance Tests

UL 486D – The 3M ITCSN tubing was subjected to the requirements of UL 486D and passed all tests. This tubing is UL Listed per UL 486D and CSA Certified.

Installation Techniques

A detailed instruction sheet regarding proper installation is included in each kit. A brief summary of the installation steps is outlined as follows:

1. Thoroughly clean and prepare cable
2. Slide 3M ITCSN tubing onto cable
3. Install connector, if applicable
4. Center tubing



5. Shrink tubing from center
6. Heat until tubing is completely shrunk and adhesive/sealant (if applicable) is squeezed from ends

3M™ Heavy Wall Heat Shrink Tubing ITCSN

Shelf Life & Storage	3M™ Heavy Wall Heat Shrink Tubing ITCSN has a 10-year shelf life from date of manufacture when stored in a humidity controlled storage (10°C/50°F to 27°C/80°F and <75% relative humidity).
---------------------------------	---

Availability	Please contact your local distributor, available from 3M.com/oem [Where to Buy] or call 1.800.676.8381
---------------------	--

Important Notice	All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product, which are not contained in 3M's current publications, or any contrary statements contained on your purchase order, shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.
-------------------------	---

Warranty; Limited Remedy; Limited Liability	This product will be free from defects in material and manufacture at the time of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.
--	---

3M is a trademark of 3M Company.



Electrical Markets Division
6801 River Place Blvd.
Austin, TX 78726-9000
800 676.8381
FAX: 800 828.9329
www.3M.com/oem

Please recycle
© 3M 2011 All rights reserved
78-8126-0422-7 C