


LOC	DIST	REVISIONS				
H	—	P	LTR	DESCRIPTION	DATE	DWN
		A		INITIAL RELEASE	16OCT2009	RC
						APVD
						AH



NOTES:

- 1
- ATTENUATION $\leq$ 0.3 dB, MEASURED AT 1310 nm
ACCORDING TO I.E.C. 61300-3-4 INSERTION METHOD B
- 2
- RETURN LOSS $\geq$ 45 dB, IN MATED CONDITION
AGAINST REFERENCE CONNECTOR AT 1310 nm
- 3
- TUNED CONNECTOR
- 4
- CABLE INFORMATION:

— CORE DIAMETER: 9/125 μ m

— OUTER JACKET DIAMETER: 0.9 mm

— OUTER JACKET COLOUR: WHITE

— OUTER JACKET MATERIAL: LSZH
- 5
- INFORMATION ON LABEL ON PLASTIC BAG


— BARCODE

— UNIQUE SERIAL NUMBER

— TYCO ELECTRONICS PART NUMBER & ORDER NUMBER

— ATTENUATION & RETURN LOSS AT 1310 nm

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	”L” (meter)
X-2061304-Y	XY.0

5	1	FOAC INFORMATION LABEL				—
	1	SC CONNECTOR, SINGLE MODE, BLUE				2
	L	FOCAB 0.9S 9/125, WHITE, LSZH				1
	Qty	Description				Item
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COOLEN 16OCT2009	Tyco Electronics Tyco Electronics Corporation 's-Hertogenbosch, Nederland			
		CHK A. HENGELMOLEN 16OCT2009				
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
mm		APVD A. HENGELMOLEN 16OCT2009	FIBER OPTIC PIGTAIL 0.9S SC/PC SINGLE MODE 9/125			
	0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± ± —	PRODUCT SPEC — APPLICATION SPEC —	SIZE A2			RESTRICTED TO —
MATERIAL —	FINISH —	WEIGHT —	CAGE CODE 00779	DRAWING NO G=2061304	SHEET 1 OF 1	
CUSTOMER DRAWING			SCALE NTS	REV A		