


Capacitor, Tantalum, SMD, Polymer, Molded, Low ESR, AEC-Q200, 220 uF, 7343, +/-20% Tol, 2.5 VDC (105C)



General Information	
Supplier:	KEMET
Brand:	Kemet
Application:	Automotive/Low ESR (AEC-Q200 Qualified)
Sub Application:	(NonCombustibleCathode)
Part Type Description:	SMD, Polymer, Molded, Low ESR, AEC-Q200
Construction:	Standard Chip-Polymer
Body Type:	Molded Chip
Footprint:	7343
Weight:	274.3 mg
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	7.3	+/-0.3
W	4.3	+/-0.3
H	1.9	+/-0.1
F	2.4	+/-0.1
S	1.3	+/-0.3
X	0.5	REF
T	0.13	REF
A	3.8	MIN

Specifications	
Capacitance:	220 uF
Tolerance:	+/-20%
Voltage:	2.5 VDC (105C)
Temperature Range:	-55/+105C
Testing:	AEC-Q200
Current/Ripple Current:	3531 mA (25C)
Current/Ripple Current:	3177.9 mA (85C)
Current/Ripple Current:	1412.4 mA (105C)
Resistance/ESR:	15 mOhms (100kHz)
Failure Rate:	NA
Leakage Current:	55 uA
Dissipation Factor:	10%

Packaging Specifications	
Package Kind:	T&R
Package Size:	7in
Package Quantity:	1000

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.