








NOTES:

1. CRIMP ACCEPTS 22 TO 26 GA. WIRE WITH (.165)/.065 MAX INSULATION DIA.
2. DIMENSIONS GIVEN ACROSS CENTERLINES ARE SYMMETRICAL ABOUT THOSE CENTERLINES WITHIN HALF THE TOTAL TOLERANCE.
3. OPTIONAL DESIGN (.86+.05)/.034+.002
4. TERMINAL CONFORMS TO PRODUCT SPEC. 08-50.
5. CAT EAR OPTION TO BE USED WITH 41695 HOUSING ONLY.




2578 - * - * - *	MATERIAL CODE	WINDING SPEC.
	(.28)/.0106 THK	A=PER ES-339-A
	BLANK=BRASS	BLANK=PER ES-339-B
	B=PHOS BRONZE	L=LOOSE
	PLATING CODE	
	(PER SDES-88)	
	OPTIONS	* (P909) OVERALL HOT TIN DIP: 2.54 MICROMETERS MIN
	BLANK=AS SHOWN	(550) SELECT GOLD: 0.38 MICROMETERS MIN.
	1=WITH CAT EARS	OVERALL GOLD FLASH: 0.05 MICROMETERS MIN.
	2=LOW INSERTION FORCE	OVERALL NICKEL UNDERPLATE: 0.76 MICROMETERS MIN.
		(555) SELECT GOLD: 0.38 MICROMETERS MIN.
		OVERALL NICKEL UNDERPLATE: 0.76 MICROMETERS MIN.

*THE PRIMARY SHIPPING CARTON WILL BE LABELED "COMPLIANT TO ROHS DIRECTIVE 2002/95/EC AND ELV ANNEX II OF DIRECTIVE 2000/53/EC." CARTONS WITHOUT THIS LABEL MAY CONTAIN PRODUCT WITH TIN-LEAD PLATING.



SECTION B-B
BACKGROUND OMITTED



SECTION A-A
BACKGROUND OMITTED

ENTER DESCRIPTION EC NO: UCP2005-0928 DRAWN BY: DRW:DAVID M. 2004/11/16 CHK'D BY: CHK'D: S. M. 2004/11/02 APPR'D BY: APPR'D: M. G. 2004/11/02 REV: W	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	 THIRD ANGLE PROJECTION	
					IN/MM			INCH		
					DRAWN BY	DATE	TITLE			
					PEREZ/AR	01/29/87	CRIMP TERMINAL			
					CHECKED BY	DATE	(3.96)/.156 CENTERS			
					PATEL	01/29/87	22 TO 26 GA WIRE			
					APPROVED BY	DATE	MOLEX INCORPORATED			
					LENZ	01/29/87				
					MATERIAL NO.		DOCUMENT NO.	SHEET NO.		
					SEE CHART		SD-2578	1 OF 2		
		SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							
		D								

	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1		
M	2578-(***)*			2578-B-(***)*			2578-B-2(***)*															
	PART NO.	ENG. NO.		PART NO.	ENG. NO.		PART NO.	ENG. NO.		PART NO.	ENG. NO.		PART NO.	ENG. NO.		PART NO.	ENG. NO.		PART NO.	ENG. NO.		M
L	08-50-0107	2578-(P909)		08-56-0121	2578-B-(501)				2578-B-2(P909)													
	08-50-0108	2578-(P909)L		08-56-0122	2578-B-(501)L				2578-B-2(P909)L													
	08-50-0111	2578-(109)		08-50-0133	2578-B-(P909)				2578-B-2(555)													
	08-50-0112	2578-(109)L		08-50-0134	2578-B-(P909)L				2578-B-2(555)L													
	08-56-0107	2578-(550)		08-65-0116	2578-B-(555)				2578-B-2(550)													
	08-56-0108	2578-(550)L		08-65-0117	2578-B-(555)L				2578-B-2(550)L													
K	08-55-0105	2578-(555)		08-65-0108	2578-B-(591)																	
	08-55-0106	2578-(555)L		08-65-0107	2578-B-(591)L																	
	08-59-0101	2578-(122)		08-60-0003	2578-B-(122)																	
	I 08-56-0162	2578-(505)		08-60-0004	2578-B-(122)L																	
	I 08-56-0163	2578-(505)L		08-65-0110	2578-B-(558)																	K
	08-50-0504	2578-(128)		08-65-0111	2578-B-(558)L																	
J		2578-(128)L		08-58-0125	2578-B-(550)																	
	08-56-0161	2578-(503)		08-58-0126	2578-B-(550)L																	
	I 08-50-0061	2578-(224)																				
	I 08-50-0062	2578-(224)L																				J
	I 08-50-0065	2578-(P224)																				
	I 08-50-0066	2578-(P224)L																				
I	08-55-0137	2578-(558)A																				
		2578-(558)L																				
	08-50-0018	2578-(102)																				
	08-50-0019	2578-(102)L																				I
	08-55-0121	2578-(561)																				
	08-55-0132	2578-(561)L																				
H	08-55-0123	2578-(558)																				
		2578-(558)L																				
	08-65-0109	2578-(555)A																				
	08-52-0116	2578-(P909)																				
	08-52-0117	2578-(P910)L																				H
G																						
F																						
E																						
D																						
C																						

CHANGE TO MEIO EC NO: UCP2005-0928 DRAWN BY: 104/11/16 CHECKED BY: 2004/11/02 APPR. MARGULIES 2004/11/02 W NEW	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	
	 	mm	INCH	DRAWN BY	DATE	TITLE			
		4 PLACES	±	±	PEREZ/AR	01/29/87	CRIMP TERMINAL		
		3 PLACES	±	±	CHECKED BY	DATE	(3.96)/.156 CENTERS		
		2 PLACES	±	±	PATEL	01/29/87	22 TO 26 GA WIRE		
		1 PLACE	±	±	APPROVED BY	DATE	MOLEX INCORPORATED		
		ANGULAR ±1/2°		LENZ	01/29/87	MOLEX INCORPORATED			
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE CHARTS		DOCUMENT NO. SD-2578		SHEET NO. 2	
				SIZE D		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			