


KEMET Part Number: C0402C223K8PACTU
(C0402C223K8PAC7867)

Capacitor, Ceramic, SMD, MLCC, Temperature Stable, Class II, 0.022 uF, +/-10% Tol, 10 V, X5R, 0402 (1005 metric)



General Information	
Supplier:	KEMET
Application:	Standard Chip
Chip Size:	0402 (1005 metric)
Temperature Coefficient:	X5R
Part Type Description:	SMD, MLCC, Temperature Stable, Class II
Termination Type:	Tin (Sn)
Marked:	No
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	1	+/-0.05
W	0.5	+/-0.05
T	0.5	+/-0.05
B	0.3	+/-0.1
S	0.3	MIN

Specifications	
Capacitance:	0.022 uF
Voltage:	10 V
Tolerance:	+/-10%
Temperature Range:	-55/+85C
Dissipation Factor:	5%
Failure Rate:	NA
Aging Rate:	4% loss/decade hour
Insulation Resistance:	10 GOhm
Dielectric Strength:	25 V
Miscellaneous:	Note: Referee time for X5R dielectric for this part number is 1000 hours

Packaging Specifications	
Package Kind:	T&R
Package Size:	7in
Package Type:	Paper Tape
Package Quantity:	10000