

## Panel mounting base - TU-0000000WB00 - 1605893


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Panel mounting base, straight, Bayonet locking, M23, Axial O-ring, 4xØ3,2, Shielded: Yes, Panel thickness min.: 1.5 mm, Cable diameter: 0 mm...0 mm



### Key commercial data

Packing unit	20 pc
GTIN	 4 046356 255516
Weight per Piece (excluding packing)	40.32 g
Custom tariff number	85366990
Country of origin	Germany

### Technical data

#### General

Note	Order information Order contact inserts separately
Type of locking	Bayonet locking
Contact connection method	Crimp connection
Type of contacts	Socket
Conductor entry	0 mm ... 0 mm
Mounting type	4xØ3,2

#### Ambient conditions

Ambient temperature	-20 °C ... 125 °C
Degree of protection	IP67

#### Material

Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Gasket and O-ring material	FPM

#### Specifications according to DIN EN 61984:2001

Installation height max.	2000 m
--------------------------	--------

# Panel mounting base - TU-0000000WB00 - 1605893

## Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260708
eCl@ss 7.0	27440312
eCl@ss 8.0	27440312

ETIM


ETIM 3.0	EC001121
ETIM 4.0	EC001121
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

## Drawings

Dimensioned drawing



Dimensioned drawing

