


To combine with heads, see pages 36160-EN/2 to 36167-EN/2



ZB5 AZ009



ZBE 101



ZBE 203




ZB5 AZ101




ZBE 201



ZB5 AZ106



ZB5 AZ107



ZBZ 001



### Body/fixing collar

For use with	Sold in lots of	Unit reference	Weight kg
Electrical block (contact or light)	10	ZB5 AZ009	0.006



### Contact functions (1)

Screw clamp terminal connections (Schneider Electric anti-retightening system)

#### Contacts for standard applications

Description	Type of contact			Sold in lots of	Unit reference	Weight kg
Contact blocks	Single	1	–	5	ZBE 101	0.011
		–	1	5	ZBE 102	0.011
	Double	2	–	5	ZBE 203	0.020
		–	2	5	ZBE 204	0.020
Single with body/fixing collar		1	1	5	ZBE 205	0.020
		1	–	1	ZB5 AZ101	0.021
		–	1	1	ZB5 AZ102	0.021
		2	–	1	ZB5 AZ103	0.030
		–	2	1	ZB5 AZ104	0.030
		1	1	1	ZB5 AZ105	0.030
		1	2	1	ZB5 AZ141	0.040

#### Contacts for specific applications

Application	Type of contact	Description			Sold in lots of	Unit reference	Weight kg	
Low power switching	Single	Standard	1	–	5	ZBE 1016	0.012	
			–	1	5	ZBE 1026	0.012	
		Dusty environment (2) (IP5X, 50 µm dust)	1	–	5	ZBE 1016P	0.012	
			–	1	5	ZBE 1026P	0.012	
Staggered contacts	Single	Early make N/O	1	–	5	ZBE 201	0.011	
			–	1	5	ZBE 202	0.011	
		Single with body/fixing collar	Overlapping N/O+N/C	1	1	5	ZB5 AZ106	0.030
			Staggered N/O+N/C	2	–	5	ZB5 AZ107	0.030
			High power switching	Single	Standard (3)	1	–	1
–	1	1				ZBE 502	0,020	
2	–	1				ZBE 503	0,032	
–	2	1				ZBE 504	0,032	
1	1	1				ZBE 505	0,032	

### Clip-on legend holder, sheet of blank legends and labelling software (4)

Description	Sold in lots of	Unit reference	Weight kg
Clip-on legend-holder for electrical blocks with screw clamp terminal connections (4). For identification of an XB5 A control or signalling unit	10	ZBZ 001	0.001
Sheet of 50 blank legends for legend holder ZBZ 001	10	ZBY 001	0.023
«SIS Label» labelling software for legend design (ZBY 001 legends) (for design of legends in English, French, German, Italian, Spanish)	1	XBZ 2U	0.100

(1) The contact blocks enable variable composition of body/contact assemblies. Maximum number of rows possible: 3. Either 3 rows of 3 single contacts or 1 row of 3 double contacts + 1 row of 3 single contacts (double contacts occupy the first 2 rows). Maximum number of contacts is specified on page 36172-EN/2.

(2) It is not possible to fit an additional contact block on the back of these contact blocks.

(3) It is not possible to fit an additional contact block on the back of these contact blocks or to use these contacts with light blocks.

(4) This legend holder is not compatible with high power switching contacts.