

PRODUCT CODE

AHG25W

PRODUCT TITLE

25 Element High Gain TV Aerial



Certification mark
digital 
Approved product



FEATURES


Sealed "F" connector dipole housing
Large reflector for good F/B ratio
Galvanised Heavy Duty Tilt Clamp
Robust 18mm boom construction
Quick assembly and set up
Ideal for weak to medium reception areas
Light grey plastics to lessen visual impact

PRODUCT SPECIFICATION

Group: Wideband
Forward Gain: 11dB(d)/13.15 dB(i)
Front to Back Ratio: >20dB
Acceptance Angle: $\pm 21.5^\circ$
Channel Number: 21-69
Frequency Range: 470-862MHz
Elements: 25
Assembled Length: 780mm
Benchmark Standard: 2

PACKAGING DETAILS

Packaging Style: Packed 5 per box. Individually poly bagged
Packaging Dimensions: W:460mm x H:840mm x D:75mm
Barcode Number: 5016163521288
Product Weight: 1.25kg (per product)
Packaging Weight: 89g (per poly bag)



Maxview Ltd, Common Lane, Setchey, King's Lynn, Norfolk, PE33 0AT.
■ Sales Line: 01553 813333 ■ Fax: 01553 813320 ■ Helpline 01553 811000

Maxview reserve the right to change specifications without prior notice