



Terminal blocks

G - Distribution terminal blocks

Summary

1. Distribution bars

Screw clamp ground terminal block	384
Connection with 18 x 3 mm collector bar	385
Bars with base for ground wire	386
Busbar clamp	387

2. Distribution terminal blocks

Phases - Ground assemblies	388
Single pole distribution blocks	390
Three pole distribution blocks	392
Four pole distribution blocks	392


Ground terminal block

Screw clamp

DIN 1 (EN 50035, DIN 46277/1, NFL 63018)

E 10/13.P

Spacing 13 mm (.512")




Characteristics			NFC	DIN	UL	CSA	NFC	DIN	UL	CSA
Wire size	Screw clamp	Rigid	0-16 mm²		16-8 AWG					
		Flexible	0-10 mm²		16-8 AWG					
Rated current			A		85					
Rated wire size			mm²/AWG		10 mm² / 8 AWG					
Other characteristics			Wire strip. length	Recomm. screwdriver	Recomm. torque	Protection	Wire strip. length	Recomm. screwdriver	Recomm. torque	Protection
			12 mm .47"	6.5 mm .25"						
Accessories			Type	Part numbers		Type	Part numbers		Type	Part numbers
1 Rail 32 x 15			PR1 Z2	1SNA 163 050 R0400						
2 Label with symbol "ground"			IDTBM	1SNA 167 357 R0400						

Distribution of polarities

If the distribution bar is longer than 1 foot (300 mm) use an intermediate end stop for support. In this case the precut bar passages need to be punched out of the end stop.


- Grey BADH 1SNA 116 900 R2700
- Grey BAEH 1SNA 116 934 R0400

Description	Types	Part numbers
Copper bar	BO3 1000 x 10 x 3 mm	1SNA 164 406 R2400
Wire clamp	SFB1 20-2 AWG (0.5-35 mm²)	1SNA 163 860 R0500
Wire clamp	SFB2 6-2 AWG (16-35 mm²)	1SNA 168 956 R0600




This end stop is also recommended :

1 - For use with neutral switch blocks series "NT"



2 - For use with separators SCFCV4 with protection cover





Connection with 18 x 3 mm collector bar

DIN 3

Shield terminals for collector bar

- Mounting on 18 x 3 mm collector bar
- Easy shield connection to a collector bar
- Brass with nickel coating clamp with a steel spring to make contact without damaging the shield
- Shield terminals available in 4 versions (shield diameter from 1,5 to 24 mm)
- Not designed for wire connection
- Mounting : place the shield of the stripped cable on the collector bar. Hold the terminal on the shield, press and snap the terminal onto the collector bar. As soon as the terminal is released, contact is made on the bar through the spring pressure.





Characteristics

Shield diameter	B (mm)	L (mm)	H max (mm)	Spring force (N)	Description	P/N
1,5 - 6,5	10	25	40	8 - 13	SFB.B1	1SNA 205 170 R1400
5 - 11	17	25	47	22 - 31	SFB.B2	1SNA 205 171 R0100
10 - 17	23	25	63	32 - 58	SFB.B3	1SNA 205 172 R0200
16 - 24	30	25	78	37 - 53	SFB.B4	1SNA 205 173 R0300

Terminals for collector bar


- 35 mm² terminal for 18 x 3 mm collector bar.
 - Stainless steel clamp and screw
 - Insulating part in polyamid 6,6 without halogen
 - Possibility to print 3 characters per marker
- If a separate ground is required, isolated mounting on rail should be made through a bar holder P/N 1SNA 205 176 R0600




SFB.P 1SNA 205 174 R0400

Bar holder (isolated from ground)

- To be screwed on plate or snapped onto DIN 3 rail
- Thermoplastic material, black colour
- Spacing : 12 mm .473"





DSPBO.PI 1SNA 205 176 R0600



Collector bar


- Electroplated copper with tin coating 18 x 3 x 1000 mm

BO 318 1SNA 205 175 R0500




Bar holder (connected to the mounting rail)

- To be snapped onto DIN 3 rail.
- Thermoplastic material, black colour.
- Tinned coated steel socket
- Spacing : 10 mm .394"





DSPBO.P 1SNA 205 177 R0700





Bars with base for ground wire

DIN 3



Blue or green base - Mounting on DIN 3 rail




Blue or green base - Mounting on DIN 3 rail

PR3.Z2		35 x 7,5 x 1	1SNA 174 300 R1700
PR4		35 x 15 x 2,3	1SNA 168 500 R1200
PR5		35 x 15 x 1,5	1SNA 168 700 R2200
Other rails : see section on accessories.			

		CE			CE
Type	P/N		Type	P/N	
7 outputs blue base	DBTI		12 outputs blue base	DBTI	
	1SNA 356 100 R1500			1SNA 356 102 R0300	
7 outputs green base	DBTI		12 outputs green base	DBTI	
	1SNA 356 101 R0200			1SNA 356 103 R0400	

Characteristics	IEC	UL	CSA	IEC	UL	CSA
Connection						
- Screw clamp						
- Max. wire size	7 outputs 10 mm²			12 outputs 10 mm²		
Torque on screw	1.5 Nm	13.3 lb.in	13.3 lb.in	1.5 Nm	13.3 lb.in	13.3 lb.in
Screw	M5	M5	M5	M5	M5	M5

Busbar clamp
10 x 3 or 6 x 6 or 15 x 6 mm
.34 x .12 or .23 x .23 or .59 x .23"
DIN 1 - 2 - 3 or panel mount




Rail		35 x 7,5 x 1	PR3.Z2	1SNA 174 300 R1700
Rail		35 x 15 x 2,3	PR4	1SNA 168 500 R1200
Rail		35 x 15 x 1,5	PR5	1SNA 168 700 R2200
Rail		32 x 15 x 1,5	PR1.Z2	1SNA 163 050 R0400

Other end stops, rails and accessories : see section on accessories.


Notes

Accessories



- 1 Locking foot
- 2 Busbar
- 3 Wire clamp

R See section on markers marking method



Colour	Type	Part number
Reversible grey clamp	SPBO	1SNA 114 712 R1300


Characteristics

Wire size		NFC	DIN	UL	CSA
Screw lamp	Rigid				
	Flexible				
Neutral bar		see beside			
Voltage					
Rated	~ AC	750 V Gr.C			
Rated	= DC	660 V Gr.C			
Pollution degree					
Current					
Rated					
Wire size					
Rated / Gauge					
Wire strip. length	Recomm. screwdriver	Recomm. torque	Protection		


Type	Part numbers
ACD13-6 for rail DIN 1 or DIN 3	1SNA 113 135 R0000
ACD23-6 for rail DIN 2 or DIN 3	1SNA 118 005 R2700
BO3 10x3 mm	1SNA 164 406 R2400
BO6 15x6 mm	1SNA 168 417 R2200
SFB1 for BO3 - 20-2 AWG (0,5-35mm²)	1SNA 163 860 R0500
SFB2 for BO3 - 6-2 AWG (16-35mm²)	1SNA 168 956 R0600
SFB3 for BO6 - 4-00 AWG (19-95mm²)	1SNA 168 690 R1000

RC610


Mounting on rail PR1 with mounting foot
ACD13-6 1SNA 113 135 R0000 (DIN 1 - DIN 3)




Mounting on rail PR2 with mounting foot
ACD23-6 1SNA 118 005 R2700 (DIN 2 - DIN 3)




Mounting on rails PR3, PR30, PR4, PR5
with mount.foot ACD13-6 1SNA 113 135 R0000 (DIN 1 - DIN 3)



with mount.foot ACD23-6 1SNA 118 005 R2700 (DIN 2 - DIN 3)




Mounting on panel by M4 screw



Various options of placing the busbars on the busbar clamp

Busbars	BO3 10 x 3	6 x 6	BO6 15 x 6
Option n° 1	X		
Option n° 2		X	
Option n° 3			X
Option n° 4	X		X
Option n° 5		X	X



Distribution terminal blocks

- phase
- ground

DIN 1-3




End stop		th. 9 mm	BADL	V0	1SNA 399 903 R0200
End stop		th. 10 mm	BAM2	V2	1SNA 206 351 R1600
End stop		th. 10 mm	BAM2 V0	V0	1SNA 296 351 R0000
Rail		35 x 7,5 x 1	PR3.Z2		1SNA 174 300 R1700
Rail		35 x 15 x 2,3	PR4		1SNA 168 500 R1200
Rail		35 x 15 x 1,5	PR5		1SNA 168 700 R2200
Rail		32 x 15 x 1,5	PR1.Z2		1SNA 163 050 R0400

Other end stops, rails and accessories : see section on accessories.

Notes


The use of some accessories may decrease the block's voltage rating. For more information, consult us.

Example of application :



The monobloc connector bar ensures perfect continuity between input and distribution. Each block has 2 Screw clamp terminals.


Accessories



1	Test socket
2	Test device
3	Test plug
4	Assembled jumper bar (without IP 20 protection)
4	Assembled jumper bar (with IP 20 protection)
5	Shield connector
R	See section on markers marking method

MB 4/6.L...
MB 4/6.P...

Spacing 6 mm (.238")




Colour	Type	Part numbers
Phases	Nb of blocks L mm	
Grey	2 14,5	MB 4/6.L2 1SNA 115 406 R1300
Grey	3 20,5	MB 4/6.L3 1SNA 115 407 R1400
Grey	4 26,5	MB 4/6.L4 1SNA 115 408 R2500
Grey	5 32,5	MB 4/6.L5 1SNA 115 409 R2600
Grey	6 38,5	MB 4/6.L6 1SNA 115 410 R1200
Grey	8 50,5	MB 4/6.L8 1SNA 115 411 R0700
Grey	10 62,5	MB 4/6.L10 1SNA 115 412 R0000
Ground (no electrical connection ro rail)		
Green-Yellow	2 14,5	MB 4/6.P2 1SNA 165 420 R2600
Green-Yellow	3 20,5	MB 4/6.P3 1SNA 165 421 R1300
Green-Yellow	4 26,5	MB 4/6.P4 1SNA 165 422 R1400
Green-Yellow	5 32,5	MB 4/6.P5 1SNA 165 423 R1500
Green-Yellow	6 38,5	MB 4/6.P6 1SNA 165 424 R1600
Green-Yellow	8 50,5	MB 4/6.P8 1SNA 165 425 R1700
Green-Yellow	10 62,5	MB 4/6.P10 1SNA 165 426 R1000

Characteristics			
Wire size		IEC	UL
		NFC DIN	CSA
Screw clamp	Rigid	0,2-4 mm ²	22-10 AWG
	Flexible	0,22-4 mm ²	22-10 AWG
Voltage			
Rated		800 V	600 V
Impulse withstand		8 kV	
Pollution degree		3	
Current			
Rated	Short-circuit	32A 300A/1s	20 A 25 A
Wire size			
Rated / Gauge		4 mm ² /A4	10 AWG 10 AWG
Wire strip. length	Recomm. screwdriver	Recomm. torque	Protection
9,5 mm	4 mm	0,5-0,8 Nm	IP20
.37"	.16"	4.5-7.1 lb.in	NEMA 1

Type	Part numbers
AL2	DIA. 2 mm 1SNA 163 043 R2100
AL3	DIA. 3 mm 1SNA 163 261 R0000
DCJ	yellow 1SNA 173 059 R0300
FC2	DIA. 2 mm 1SNA 007 865 R2600
BJM6	2 to 10 poles (1)
BJMI6	2 to 10 poles (1)
CBM5	th. 0,5 mm 1SNA 178 745 R1400
CBM8	th. 0,8 mm 1SNA 178 746 R1500
RC65 - RC610	
Note : (1) See section : accessories	

MB 6/8.L...
MB 6/8.P...

Spacing 8 mm (.315")



Colour	Type	Part numbers
Phases	Nb of blocks L mm	
Grey	2 18,5	MB 6/8.L2 1SNA 115 413 R0100
Grey	3 26,5	MB 6/8.L3 1SNA 115 414 R0200
Grey	4 34,5	MB 6/8.L4 1SNA 115 415 R0300
Grey	5 42,5	MB 6/8.L5 1SNA 115 416 R0400
Grey	6 50,5	MB 6/8.L6 1SNA 115 417 R0500
Grey	8 66,5	MB 6/8.L8 1SNA 115 418 R1600
Grey	10 82,5	MB 6/8.L10 1SNA 115 419 R1700
Ground (no electrical connection ro rail)		
Green-Yellow	2 18,5	MB 6/8.P2 1SNA 165 427 R1100
Green-Yellow	3 26,5	MB 6/8.P3 1SNA 165 428 R2200
Green-Yellow	4 34,5	MB 6/8.P4 1SNA 165 429 R2300
Green-Yellow	5 42,5	MB 6/8.P5 1SNA 165 430 R2000
Green-Yellow	6 50,5	MB 6/8.P6 1SNA 165 431 R1500
Green-Yellow	8 66,5	MB 6/8.P8 1SNA 165 432 R1600
Green-Yellow	10 82,5	MB 6/8.P10 1SNA 165 433 R1700

Characteristics			
Wire size		IEC	UL
		NFC DIN	CSA
Screw clamp	Rigid	0,5-10 mm ²	22-8 AWG
	Flexible	0,5-6 mm ²	22-8 AWG
Voltage			
Rated		800 V	600 V
Impulse withstand		8 kV	
Pollution degree		3	
Current			
Rated	Short-circuit	41A 720A/1s	50 A 35 A
Wire size			
Rated / Gauge		6 mm ²	8 AWG 8 AWG
Wire strip. length	Recomm. screwdriver	Recomm. torque	Protection
12 mm	4-5 mm	0,8-1 Nm	IP20
.47"	.16-.20"	7.1-8.9 lb.in	NEMA 1

Type	Part numbers
AL2	DIA. 2 mm 1SNA 163 043 R2100
AL3	DIA. 3 mm 1SNA 163 261 R0000
AL4	DIA. 4 mm 1SNA 163 262 R0100
DCO	orange 1SNA 173 060 R0000
FC2	DIA. 2 mm 1SNA 007 865 R2600
FC4	DIA. 4 mm 1SNA 167 860 R0100
BJM8	2 to 10 poles (1)
BJMI8	2 to 10 poles (1)
RC810	

MB 10/10.L...

MB 10/10.P...

Spacing 10 mm (.394")

NFC : 71 A max./pole
CSA : 50 A max./pole
UL : 65 A max./pole

130 A max. (UL)

input rated wire size 2x6 AWG (2x16 mm²)
distribution output rated wire size 6 AWG (16 mm²)

MB 70/10.L...

MB 70/10.P...

Spacing 10 mm (.394") with single connection point

NFC : 71 A max./pole
CSA : 65 A max./pole
UL : 65 A max./pole

239 A max.
200 A max.

71 A max./pole
65 A max./pole

128 A (NFC)
100 A (UL/CSA)

128 A (NFC)
100 A (UL/CSA)

distribution output rated wire size 6 AWG (16 mm²)
input rated wire size 1 x 00 AWG (1 x 70 mm²)
distribution output rated wire size 6 AWG (16 mm²)

MB 2x70/10.L...

MB 2x70/10.P...

Spacing 10 mm (.394") with double connection point

NFC : 71 A max./pole
CSA : 65 A max./pole
UL : 65 A max./pole

256 A max.
200 A max.

71 A max./pole
65 A max./pole

128 A (NFC)
100 A (UL/CSA)

128 A (NFC)
100 A (UL/CSA)

distribution output rated wire size 6 AWG (16 mm²)
input rated wire size 1 x 00 AWG (1 x 70 mm²)
distribution output rated wire size 6 AWG (16 mm²)

Colour	Type	Part numbers
Phases	Nb of L blocks mm	
Grey	2 22,5	MB 10/10.L2 1SNA 115 328 R2300
Grey	3 32,5	MB 10/10.L3 1SNA 115 329 R2400
Grey	4 42,5	MB 10/10.L4 1SNA 115 330 R2100
Grey	5 52,5	MB 10/10.L5 1SNA 115 331 R1600
Grey	6 62,5	MB 10/10.L6 1SNA 115 332 R1700
Grey	8 82,5	MB 10/10.L8 1SNA 115 333 R1000
Grey	10 102,5	MB 10/10.L10 1SNA 115 334 R1100
Ground (no electrical connection to rail)		
Green-Yellow	2 22,5	MB 10/10.P2 1SNA 165 343 R0400
Green-Yellow	3 32,5	MB 10/10.P3 1SNA 165 344 R0500
Green-Yellow	4 42,5	MB 10/10.P4 1SNA 165 345 R0600
Green-Yellow	5 52,5	MB 10/10.P5 1SNA 165 346 R0700
Green-Yellow	6 62,5	MB 10/10.P6 1SNA 165 347 R0000
Green-Yellow	8 82,5	MB 10/10.P8 1SNA 165 348 R1100
Green-Yellow	10 102,5	MB 10/10.P10 1SNA 165 349 R1200

Colour	Type	Part numbers
Phases	Nb of L blocks mm	
Grey	2x1 54	MB 70/10.L2 1SNA 115 335 R1200
Grey	2x2 74	MB 70/10.L4 1SNA 115 336 R1300
Grey	2x3 94	MB 70/10.L6 1SNA 115 337 R1400
Grey	2x4 114	MB 70/10.L8 1SNA 115 338 R2500
Ground (no electrical connection to rail)		
Green-Yellow	2x1 54	MB 70/10.P2 1SNA 165 350 R1700
Green-Yellow	2x2 74	MB 70/10.P4 1SNA 165 351 R0400
Green-Yellow	2x3 94	MB 70/10.P6 1SNA 165 352 R0500
Green-Yellow	2x4 114	MB 70/10.P8 1SNA 165 353 R0600

Colour	Type	Part numbers
Phases	Nb of L blocks mm	
Grey	2x4 143	MB 2x70/10.L8 1SNA 115 342 R2100
Ground (no electrical connection to rail)		
Green-Yellow	2x4 143	MB 2x70/10.P8 1SNA 165 357 R0200

Characteristics			
Wire size	IEC	UL	CSA
	NFC DIN		
Compression clamp	Rigid 0,5-16 mm²	22-6 AWG	18-6 AWG
	Flexible 0,5-10 mm²	22-6 AWG	18-6 AWG
Voltage			
Rated	800 V	600 V	600 V
Impulse withstand	8 kV		
Pollution degree	3		
Current			
Rated	Short-circuit 63A 1200A/1s	65 A	50 A
Wire size			
Rated / Gauge	10 mm²	6 AWG	6 AWG
Wire strip. length	Recomm. screwdriver	Recomm. torque	Protection
12 mm	5,5-6 mm	1,2-1,4 Nm	IP20
.47"	.22-.24"	10.6-12.3 lb.in	NEMA 1

Characteristics			
Wire size	IEC	UL	CSA
	NFC DIN		
Compression clamp	Rigid 0,5-16 mm²	22-6 AWG	14-6 AWG
	Flexible 0,5-10 mm²	22-6 AWG	14-6 AWG
	Max. 95 mm²	00 AWG	00 AWG max.
Lugs	Rated 70 mm²	00 AWG	00 AWG max.
Voltage			
Rated	800 V	600 V	600 V
Impulse withstand	8 kV		
Pollution degree	3		
Current			
Rated	Short-circuit 63A 1200A/1s	200 A	200 A
Wire size			
Rated / Gauge	10 mm²	6 AWG	6 AWG
Wire strip. length	Recomm. screwdriver	Recomm. torque (screws)	Recomm. torque (lugs)
12 mm	5,5-6 mm	1,2-1,4 Nm	6 Nm
.47"	.22-.24"	10.6-12.3 lb.in	52 lb.in

Characteristics			
Wire size	IEC	UL	CSA
	NFC DIN		
Compression clamp	Rigid 0,5-16 mm²	22-6 AWG	14-6 AWG
	Flexible 0,5-10 mm²	22-6 AWG	14-6 AWG
	Max. 2x95 mm²	00 AWG	00 AWG max.
Lugs	Rated 2x70 mm²	00 AWG	00 AWG max.
Voltage			
Rated	800 V	600 V	600 V
Impulse withstand	8 kV		
Pollution degree	3		
Current			
Rated	Short-circuit 63A 1200A/1s	200 A	200 A
Wire size			
Rated / Gauge	10 mm²	6 AWG	6 AWG
Wire strip. length	Recomm. screwdriver	Recomm. torque (screws)	Recomm. torque (lugs)
12 mm	5,5-6 mm	1,2-1,4 Nm	6 Nm
.47"	.22-.24"	10.6-12.3 lb.in	52 lb.in

Type	Part numbers
AL2	DIA. 2 mm 1SNA 163 043 R2100
AL3	DIA. 3 mm 1SNA 163 261 R0000
AL4	DIA. 4 mm 1SNA 163 262 R0100
FC2	DIA. 2 mm 1SNA 007 865 R2600
FC4	DIA. 4 mm 1SNA 167 860 R0100
BJM10	2 to 10 poles (1)
BJMI10	2 to 10 poles (1)
RC65 - RC610	RC810 RC1010


Type	Part numbers
AL2	DIA. 2 mm 1SNA 163 043 R2100
AL3	DIA. 3 mm 1SNA 163 261 R0000
AL4	DIA. 4 mm 1SNA 163 262 R0100
FC2	DIA. 2 mm 1SNA 007 865 R2600
FC4	DIA. 4 mm 1SNA 167 860 R0100
BJM10	2 to 4 poles (1)
BJMI10	2 to 4 poles (1)
RC65 - RC610	RC810 RC1010

Type	Part numbers
AL2	DIA. 2 mm 1SNA 163 043 R2100
AL3	DIA. 3 mm 1SNA 163 261 R0000
AL4	DIA. 4 mm 1SNA 163 262 R0100
FC2	DIA. 2 mm 1SNA 007 865 R2600
FC4	DIA. 4 mm 1SNA 167 860 R0100
BJM10	2 to 4 poles (1)
BJMI10	2 to 4 poles (1)
RC65 - RC610	RC810 RC1010

Note : (1) See section : accessories

Single pole distribution blocks

 DIN 3



BADL		th. 9 mm	V0 1SNA 399 903 R0200
BAM2		th. 10 mm	V2 1SNA 206 351 R1600
BAM2 V0		th. 10 mm	V0 1SNA 296 351 R0000
BADH		th. 12 mm	V2 1SNA 116 900 R2700
BAMH		th. 9,1 mm	V2 1SNA 114 836 R0000
BAMH V0		th. 9,1 mm	V0 1SNA 194 836 R0100
PR3.Z2		35 x 7,5 x 1	1SNA 174 300 R1700
PR4		35 x 15 x 2,3	1SNA 168 500 R2100
PR5		35 x 15 x 1,5	1SNA 168 700 R2200

Other end stops, rails and accessories : see section on accessories


Characteristics

Rated voltage	
Rated current	
Inputs	(maximum wire size) left input wire size right input wire size
Recommended torque	
Recommended torque wrench	
Outputs	with ferrules without ferrules
Recommended torque	
wire size with/without ferrule	
Recommended torque	
wire size with or without ferrule	
Recommended torque	
Screwdriver	

Accessories

[illegible]


BRU 80 A




Three holes on unit top allow wire entry from top or bottom.
Rail (DIN 3) or base mount with 2 x M5 screws. Unit may be mounted horizontally or vertically.
Finger contact protection IP 20.

			
Type		P/N	
Grey body			
BRU 80 A	1SNA 356 208 F2500		

BRU 125 A




Rail (DIN 3) or base mounted (M5 screw)
Colour : grey



Jumper bar : 2 spades 20 mm² or
8 spades 20 mm² (to be cut)

 US	
Type	P/N
Grey body	
BRU 125 A	1SNA 356 204 R1100

BRU 160 A



Rail (DIN 3) or base mounted (M5 screw)
Colour : grey

		
Type	P/N	
Gray body		
BRU 160 A	1SNA 356 200	R2100

IEC	UL/CSA
-----	--------

690 V	600 V
80 A	80 A
2,5 - 16 mm ²	14 - 4 AWG
1.5 Nm	1.5 Nm
2 x 16 mm ²	14 AWG to 4 AWG
1,5 Nm	1,5 Nm
4 x 2.5 to 6 mm ²	14 AWG to 10 AWG
0.8 Nm	0.8 Nm
Posidriv Z2 or flat	
Weight	
73 gr	
0.16 lb	

IEC U


690 V	600 V
125 A	125 A
10 -35 mm ²	8 -2 AWG
6 -16 mm ²	10 -6 AWG
3,5 Nm	31 lb.in
Allen key/4 mm	Allen key/4 mm
4 x 2,5 to 16 mm ²	14 AWG to 6 AWG
6 x 2,5 to 16 mm ²	14 AWG to 6 AWG
2 Nm	17.6 lb.in
Posidriv Z2 or flat	
Weight	
137 gr	
0.3 lb	

IEC	U
-----	---

[illegible]

Single pole distribution blocks

 DIN 3



BADL		th. 9 mm	V0 1SNA 399 903 R0200
BAM2		th. 10 mm	V2 1SNA 206 351 R1600
BAM2 V0		th. 10 mm	V0 1SNA 296 351 R0000
BADH		th. 12 mm	V2 1SNA 116 900 R2700
BAMH		th. 9,1 mm	V2 1SNA 114 836 R0000
BAMH V0		th. 9,1 mm	V0 1SNA 194 836 R0100
PR3,Z2		35 x 7,5 x 1	1SNA 174 300 R1700
PR4		35 x 15 x 2,3	1SNA 168 500 R1200
PR5		35 x 15 x 1,5	1SNA 168 700 R2200



Other end stops, rails and accessories : see section on accessories

Characteristics

Rated voltage
Rated current
Input (min. - max. wire size)
Recommended torque
Allen key
Outputs
wire size with ferrule
wire size without ferrule
Recommended torque
wire size with/without ferrule
Recommended torque
wire size with or without ferrule
Recommended torque

Accessories

BRU 175





	
Type	P/N
Grev body	BRU 175 1SNA 356 212 F0000

[illegible]

Weight
230 gr
0.507 lb

[illegible]

BRU 250 A



		
Type	P/N	
Grey body	BRU 250 A	1SNA 179 657 R1500
Black body	BRU 250 AII	1SNA 356 207 R1400

IEC	UL/CSA
690 V	600 V
250 A	230 A
35 - 120 mm ²	2 - 0000 AWG
19 Nm	170 lb.in
6 flats/6 mm	6 flats/6 mm
2 x 2,5 to 25 mm ²	2x14AWG to 4AWG
2 x 2,5 to 35 mm ²	2x14AWG to 2AWG
3,5 Nm	31 lb.in
5 x 2,5 to 16 mm ²	5x14AWG to 6AWG
2 Nm	18 lb.in
4 x 2,5 to 10 mm ²	4x14AWG to 8AWG
2 Nm	18 lb.in

Weight	
BRU 250 A	BRU 250 ALU
450 gr	220 gr
0.992 lb	0.485 lb

[illegible]

BRU 400 A

		
Type	P/N	
Grey body		
BRU 400 A	1SNA 179 650 R2200	

IEC	UL/CSA
690 V	600 V
400 A	310 A
95 - 185 mm ²	000 AWG - 350 MCM
25 Nm	230 lb.in
6 flats/8 mm	6 flats/8 mm
2 x 2,5 to 25 mm ²	2x14AWG to 4AWG
2 x 2,5 to 35 mm ²	2x14AWG to 2AWG
3,5 Nm	31 lb.in
5 x 2,5 to 16 mm ²	5x14AWG to 6AWG
2 Nm	18 lb.in
4 x 2,5 to 10 mm ²	4x14AWG to 8AWG
2 Nm	18 lb.in

Weight
450 gr
0.992 lb

[illegible]

