


dimensions in mm

**K24 • 0** ☉☉

Ratio	☉☉	5	8	20	32	64	128	320	800	2048
No. of gear stages		2	2	4	4	4	4	6	6	6
Direction of Rotation		=	=	=	=	=	=	=	=	=
Efficiency		0.85	0.85	0.75	0.75	0.75	0.75	0.65	0.65	0.65
L (mm)		15	15	18	18	18	18	21	21	21
Mass (g)		15	15	18	18	18	18	20	20	20
<b>Available with motor</b>										
22N28 • 286/22N 48 • 308										
22V28 • 202/22V 48 • 225										
23V58 • 4/23V48 • 11										
26N58 • 5/26N48 • 9										
P310 • 9										

Characteristics		K24 • 0	K24 2R • 0
Bearing Type		sleeve	ball
Max. static torque	Nm (oz-in)	0.7 (100)	0.7 (100)
Max. radial force at 8 mm from mounting face	N (lb)	5 (1.1)	20 (4.5)
Max. axial force	N (lb)	8 (1.8)	10 (2.2)
Force for press-fit	N (lb)	30 (6.7)	30 (6.7)
Average backlash at no-load		1.5°	1.5°
Average backlash at 0.12 Nm		2.5°	2.5°
Radial play	µm	≤40	≤10
Axial play	µm	50-150	≤10
Max. recom. input speed	rpm	5000	5000
Operating temperature range	°C (°F)	-30...+65 (-22...+150)	



DANAHER MOTION is a trademark of Danaher Corporation. Danaher Motion makes every attempt to ensure accuracy and reliability of the specifications in this publication. Specifications are subject to change without notice. Danaher Motion provides this information "AS IS" and disclaims all warranties, express or implied, including, but not limited to, implied warranties of merchantability and fitness for a particular purpose. It is the responsibility of the product user to determine the suitability of this product for a specific application. ©2004 Danaher Motion.