



### Main

Range of product	NG125
Device short name	MN
Product or component type	Undervoltage release
Control circuit voltage	230...240 V AC 50/60 Hz
Control type	Standard
9 mm pitches	2

### Complementary

[Ui] rated insulation voltage	690 V AC 50/60 Hz conforming to EN/IEC 60947-5-1
[Uimp] rated impulse withstand voltage	8 kV conforming to EN/IEC 60947-5-1
Local signalling	Action indicator
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
Height	103 mm
Width	18 mm
Depth	69 mm
Electrical durability	10000 cycles conforming to EN/IEC 60947-5-1
Connections - terminals	Plate terminal 2 cable(s) 1.5 mm <sup>2</sup> rigid Plate terminal 1 cable(s) 2.5 mm <sup>2</sup> rigid Plate terminal 1 cable(s) 2.5 mm <sup>2</sup> flexible Plate terminal 2 cable(s) 1.5 mm <sup>2</sup> flexible
Wire stripping length	9 mm
Tightening torque	1 N.m

### Environment

Standards	EN/IEC 60947-5-1
Product certifications	ASEFA ASTA KEMA LCIE
IP degree of protection	IP4 conforming to EN/IEC 60947-5-1 IP20 B conforming to EN/IEC 60947-5-1
Pollution degree	3 conforming to EN/IEC 60947-5-1
Overvoltage category	II
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 55 °C
Ambient air temperature for storage	-40...70 °C

### Contractual warranty

Period	18 months
--------	-----------