


## EPIC® H-B 48 AD-LB

Housing design H-B for 2 inserts.

The robust, large housing consists of the pivots for a single lever, a seal and a thermoplastic cap and is suitable for investment construction applications.



### Benefits

The large, robust housing for two inserts in one connector. Power and data in a single connector

### Application range

Plant engineering  
Plastics industry

### Product features

Panel-mount base  
Single lever  
Plastic cover  
Included: flat gasket

### Technical Data

Classification:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched)
Temperature range:	-40°C to +100°C, short-term up to +125°C

### Note

Photographs are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.



**EPIC® H-B 48 AD-LB**

Article number	Article description
H-B housing: panel-mount base (cover, single lever)	
10152000	H-B 48 AD-LB

Last Update (23.09.2017)

©2017 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16