



THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	AUGUST , 2005.
© COPYRIGHT 2005	BY TYCO ELECTRONICS CORPORATION.	ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		C	ECR-05-006587	02AUG05	JMS	FWK

- NOTES:
- ⚠ SINGLE PACK IN ACCORDANCE WITH AMP SPEC 107-3275
 - ⚠ 50 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
 - ⚠ Au PLATING OVER Ni PLATING OVER Cu PLATING
 - ⚠ Ni PLATING OVER Cu PLATING
 - ⚠ TIN PLATING
 - ⚠ RECOMMENDED SELF-TAPPING SCREW 221108-4
 - 7. RECOMMENDED MOUNT NUT 1-1634816-0
 - 8. RECOMMENDED LOCKWASHER 1-1634817-0
 - 9. CHARACTERISTICS
FREQUENCY RANGE: DC - 4GHz
NOMINAL IMPEDANCE: 50 OHMS
WORKING VOLTAGE: 500V RMS
INSULATION RESISTANCE: 5000 MOHMS
DIELECTRIC WITHSTAND VOLTAGE: 1500V RMS
CONTACT RESISTANCE: 1.5 mOHMS
CENTRE CONTACT: 0.2 mOHMS
OUTER CONTACT
 - 10. MECHANICAL CHARACTERISTICS
DURABILITY: 50 CYCLES
 - 11. FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE
 - 12. ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED



1	1	1	1	1	1	ZINC DIECAST	⚠	BODY	7
-	-	2	2	-	-	BRASS	⚠	BOARD LOCK	6
-	-	-	-	2	2	BRASS	⚠	MOUNTING POST	5
1	1	1	1	1	1	BRASS	⚠	SOLDER TAIL	4
1	1	1	1	1	1	PE-606		INSULATOR	3
1	1	1	1	1	1	PBT WHITE		HOUSING	2
1	1	1	1	1	1	BRASS	⚠	CONTACT	1
6--2	1--2	6--1	1--1	6--0	1--0	MATERIAL		DESCRIPTION	ITEM
⚠	⚠	⚠	⚠	⚠	⚠				

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	J.SANDWELL	02AUG05	tyco <i>Electronics</i> Tyco Electronics Corporation Bideford, UK, EX39 4HE			
DIMENSIONS: mm		CHK	S.PARLOW	02AUG05				
		TOLERANCES UNLESS OTHERWISE SPECIFIED			NAME			
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH			F.WHEELER-KING			
MATERIAL		SEE TABLE			108-3435			
SEE TABLE		SEE TABLE			APPLICATION SPEC			
					N/A			
					WEIGHT -			
					CUSTOMER DRAWING			
					SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
					A2	00779	C=1337543	-
					SCALE NTS			
					SHEET	1	OF 1	REV C