


DO NOT SCALE

DIMENSIONS IN mm



METRIC

THIRD ANGLE  
PROJECTION




NOTES:

- ① CONNECTOR IS DESIGNED FOR FLAT RIBBON CABLE ON 1,27 CENTERS . FOR CABLE REQUIREMENTS SEE AMP APPLICATION SPECIFICATION 114-19022.
- ② THESE RECEPTACLE CONNECTORS MATE WITH  $0,64^{+0,05}$  mm SQUARE OR ROUND POSTS ON 2,54mm GRID.
- ③ MARK INDICATING FIRST CABLE POSITION REFERRING TO CONTACT POSITION.
- ④ THERE IS NO POLARIZATION-SLOT AT THIS END IN 6, 10 AND 14 POS CONNECTORS.
- ⑤ THESE CONNECTORS CAN BE USED IN CONJUNCTION WITH STRAIN-RELIEF COVERS OF PARTNR: 100103.
- ⑥ THERE IS NO POLARIZATION-SLOT AT THIS END IN 6 POS CONNECTORS.
- ⑦ PRODUCT SPECIFICATION 108-19033.
- ⑧ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI  $\pm 0,15$




CONNECTOR HEIGHT AFTER CABLE TERMINATION. ①



⑧ OBSOLETE

⑧ OBSOLETE

QUANTITY PER REEL	DIM. "C"	"B" CABLE POS.	"A" DUAL POS.	PARTNUMBER	PART REV.
1000	85,9	64	32	6-215915-4	D
1000	80,8	60	30	6-215915-0	D
1000	68,1	50	25	5-215915-0	D
1500	60,5	44	22	4-215915-4	D
1500	55,4	40	20	4-215915-0	D
1500	47,8	34	17	3-215915-4	D
1500	42,7	30	15	3-215915-0	D
1500	37,6	26	13	2-215915-6	D
1500	30,0	20	10	2-215915-0	D
1500	24,9	16	8	1-215915-6	D
1500	22,4	14	7	1-215915-4	D
1500	17,3	10	5	1-215915-0	D
OBSOLETE	1500	14,8	8	0-215915-8	B
1500	12,2	6	3	0-215915-6	D
OBSOLETE	1500	9,7	4	0-215915-4	B



③ RECEPTACLE CONTACT	PHOSPHORBRONZE Cu Sn6	AT CONTACT-PLACE: 0,8μ GOLD AT WIRING END: 2,5μ TIN ENTIRE UNDERCOATING: 1,27μ NICKEL
② COVER	THERMOPLASTIC POLYESTER GF UL 94 -V0	GREY RAL 7032 ONLY FOR REF.
① HOUSING		

COMPONENT NAME	MATERIAL	PLATING / COLOUR
D6 ECO-09-020935	KK AEG 31AUG09	CUSTOMER DRAWING FOR REFERENCE ONLY WILL NOT BE UPDATED
D5 ECR06-29576	A.V. R.M. 15-12-06	© COPYRIGHT 19 - BY AMP HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED.AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.
D4 ET00-0243-04	A.V. R.M. 21-03-05	THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION
D3 ET00-0159-04	A.V. R.M. 13-07-04	
D2 ET00-0180-03	A.V. R.M. 19-01-04	
D1 ET00-0093-03	SS - 23-05-03	
D H-7482	JvL RV 29-10-92	

D7 ECR-10-026086	S.C	L.SM	21-12-10	LTR.	REVISION RECORD	DR.	CHK.	DATE	DR. R.HOGEVEEN	CHK. R.VERSTUJEN	APP. LV.SOEST	DWG.No. C-215915	SIZE A3	SHEET 1 OF 1	REV.LTR. D7
LTR.	REVISION RECORD	DR.	CHK.	DATE	DR. R.HOGEVEEN	CHK. R.VERSTUJEN	APP. LV.SOEST	DATE: 02-02-88	DATE: 03-02-88	DATE: 03-02-88					