


Printed-circuit board connector - FMC 0,5/10-ST-2,54 C1 - 1706253

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Plug component, Nominal current: 6 A, Rated voltage (III/2): 160 V, Number of positions: 10, Pitch: 2.54 mm, Connection method: Spring-cage connection, Color: black, Contact surface: Gold, Fixed coding of the first position, can be combined with MC(V) 0,5/...-G-2,54...C1 headers



Key commercial data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 046356 841184
Weight per Piece (excluding packing)	22220.0 g
Custom tariff number	85366990
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length	15.4 mm
Height	5.4 mm
Width	25.86 mm
Pitch	2.54 mm
Dimension a	22.86 mm

General

Range of articles	FMC 0,5/...-ST
Insulating material group	IIIa
Rated surge voltage (III/3)	2.5 kV
Rated surge voltage (III/2)	2.5 kV
Rated surge voltage (II/2)	2.5 kV
Rated voltage (III/3)	32 V
Rated voltage (III/2)	160 V
Rated voltage (II/2)	160 V

Printed-circuit board connector - FMC 0,5/10-ST-2,54 C1 - 1706253

Technical data

General

Connection in acc. with standard	EN-VDE
Nominal current I _N	6 A
Nominal cross section	0.5 mm ²
Insulating material	LCP
Inflammability class according to UL 94	V0
Stripping length	7 mm
Number of positions	10

Connection data

Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	0.5 mm ²
Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	0.5 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	0.34 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	0.25 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	20

Classifications

eCl@ss

eCl@ss 4.0	27141109
eCl@ss 4.1	27141109
eCl@ss 5.0	27141190
eCl@ss 5.1	27141190
eCl@ss 6.0	27261101
eCl@ss 7.0	27440402
eCl@ss 8.0	27440309

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002643
ETIM 5.0	EC002638

UNSPSC

UNSPSC 6.01	30211801
UNSPSC 7.0901	39121432
UNSPSC 11	39121432

Printed-circuit board connector - FMC 0,5/10-ST-2,54 C1 - 1706253

Classifications

UNSPSC

UNSPSC 12.01	39121432
UNSPSC 13.2	39121432

Accessories

Accessories

Connector

Ferrule - A 0,25- 7 - 3202478



Ferrule, Length: 7 mm, Color: silver

Ferrule - A 0,34- 7 - 3009202



Ferrule, Length: 7 mm, Color: silver

Crimping tool

Crimping pliers - CRIMPFOX 6 - 1212034



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.25 mm² ... 6.0 mm², lateral entry, trapezoidal crimp

Labeled terminal marker

Marker card - SK 2,54/2,8:FORTL.ZAHLEN - 0804853



Marker card, Card, white, labeled, Horizontal: Consecutive numbers 1 - 10, 11 - 20, etc. up to 91 - 99, Mounting type: Adhesive, for terminal block width: 2.54 mm, Lettering field: 2.54 x 2.8 mm

Screwdriver tools

Printed-circuit board connector - FMC 0,5/10-ST-2,54 C1 - 1706253

Accessories

Screwdriver - SZS 0,4X2,0 - 1205202



Micro screwdriver, bladed, size: 0.4 x 2.0 x 60 mm, 2-component grip, with non-slip grip and twist cap

Additional products

Base strip - MC 0,5/10-G-2,54 P20THRR44C1 - 1706214



Header, Nominal current: 6 A, Rated voltage (III/2): 160 V, Number of positions: 10, Pitch: 2.54 mm, Color: black, Contact surface: Gold, Mounting: Taped SMD/THT/THR components, Fixed coding of the first position, can be combined with the FMC 0,5/...-ST-2,54 C1 connector

Base strip - MCV 0,5/10-G-2,54 P20THRR56C1 - 1706178



Header, Nominal current: 6 A, Rated voltage (III/2): 160 V, Number of positions: 10, Pitch: 2.54 mm, Color: black, Contact surface: Gold, Mounting: Taped SMD/THT/THR components, Fixed coding of the first position, can be combined with the FMC 0,5/...-ST-2,54 C1 connector

Base strip - MC 0,5/10-G-2,54 SMDR44C1 - 1706140



Header, Nominal current: 6 A, Rated voltage (III/2): 160 V, Number of positions: 10, Pitch: 2.54 mm, Color: black, Contact surface: Gold, Mounting: Taped SMD/THT/THR components, Fixed coding of the first position, can be combined with the FMC 0,5/...-ST-2,54 C1 connector

Base strip - MCV 0,5/10-G-2,54 SMDR56C1 - 1706102



Header, Nominal current: 6 A, Rated voltage (III/2): 160 V, Number of positions: 10, Pitch: 2.54 mm, Color: black, Contact surface: Gold, Mounting: Taped SMD/THT/THR components, Fixed coding of the first position, can be combined with the FMC 0,5/...-ST-2,54 C1 connector

Drawings

Printed-circuit board connector - FMC 0,5/10-ST-2,54 C1 - 1706253

Dimensioned drawing

