

Belden Wire & Cable - Paired Cable

Mid-High Capacitance Computer Cable

Overall Beldfoil® Shield

24 AWG, 3 Pairs

For EIA RS-232 Applications

Trade Number: 9503

Plenum Versions: 89503

NEC CMG  
UL AWM 2464  
CSA AWM  
CEC CMG

Conductor AWG: 24  
Conductor Stranding: (7x32)  
Conductor Type: TC  
Conductor DCR: 24 ohms/M'

Insulation Type: S-R PVC

Jacket Type: PVC

Shield Type: Beldfoil

Nominal OD: 0.232 in.

Nominal Capacitance: 30 pF/ft\*

Nominal Capacitance: 50 pF/ft\*\*

Velocity of Prop.: 60%

**Standard Lengths(ft.) Standard Units(lbs.)**

100	3.3
U-500	14.7
500	15.3
U-1000	28.7
1000	29.6

Frequency(Mhz)	Max. Atten(dB/M')	Min. NEXT(dB)
----------------	-------------------	---------------

**DESCRIPTION**

Tinned copper, S-R PVC insulated, twisted pairs. Overall Beldfoil® aluminum-polyester shield. 24 AWG stranded tinned copper drain wire. Chrome PVC jacket. 100% shield coverage.

Rating: 300V 80°C

\*Capacitance between conductors.

\*\*Capacitance between one conductor and other conductors connected to shield.