





LOC	DIST	REVISIONS					
AD	39	P	LTR	DESCRIPTION	DATE	DWN	APVD
			H2	REVISED PER ECO-11-004820	11MAR11	RK	HMR



- | | |
|---|--|
| 1 | THIS COVER WILL MATE WITH COVER HALVES 102540, 102541, OR 102537 |
| 2 | MATERIAL: FLAME RETARDANT THERMOPLASTIC,
COLOR-BLACK |
| 3 | OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI |

OBSOLETE	91.44[.3.600]	88.90[.3.500]	35	72	3-102536-4
OBSOLETE	88.90[.3.500]	86.36[.3.400]	34	70	3-102536-3
OBSOLETE	86.36[.3.400]	83.82[.3.300]	33	68	3-102536-2
OBSOLETE	83.82[.3.300]	81.28[.3.200]	32	66	3-102536-1
	81.28[.3.200]	78.74[.3.100]	31	64	3-102536-0
OBSOLETE	78.74[.3.100]	76.20[.3.000]	30	62	2-102536-9
	76.20[.3.000]	73.66[.2.900]	29	60	2-102536-8
OBSOLETE	73.66[.2.900]	71.12[.2.800]	28	58	2-102536-7
OBSOLETE	71.12[.2.800]	68.58[.2.700]	27	56	2-102536-6
OBSOLETE	68.58[.2.700]	66.04[.2.600]	26	54	2-102536-5
OBSOLETE	66.04[.2.600]	63.50[.2.500]	25	52	2-102536-4
	63.50[.2.500]	60.96[.2.400]	24	50	2-102536-3
OBSOLETE	60.96[.2.400]	58.42[.2.300]	23	48	2-102536-2
OBSOLETE	58.42[.2.300]	55.88[.2.200]	22	46	2-102536-1
OBSOLETE	55.88[.2.200]	53.34[.2.100]	21	44	2-102536-0
OBSOLETE	53.34[.2.100]	50.80[.2.000]	20	42	1-102536-9
	50.80[.2.000]	48.26[.1.900]	19	40	1-102536-8
OBSOLETE	48.26[.1.900]	45.72[.1.800]	18	38	1-102536-7
OBSOLETE	45.72[.1.800]	43.18[.1.700]	17	36	1-102536-6
	43.18[.1.700]	40.64[.1.600]	16	34	1-102536-5
√ OBSOLETE	40.64[.1.600]	38.10[.1.500]	15	32	1-102536-4
	38.10[.1.500]	35.56[.1.400]	14	30	1-102536-3
	35.56[.1.400]	33.02[.1.300]	13	28	1-102536-2
	33.02[.1.300]	30.48[.1.200]	12	26	1-102536-1
	30.48[.1.200]	27.94[.1.100]	11	24	1-102536-0
√ OBSOLETE	27.94[.1.100]	25.40[.1.000]	10	22	102536-9
	25.40[.1.000]	22.86[.900]	9	20	102536-8
	22.86[.900]	20.32[.800]	8	18	102536-7
	20.32[.800]	17.78[.700]	7	16	102536-6
	17.78[.700]	15.24[.600]	6	14	102536-5
	15.24[.600]	12.70[.500]	5	12	102536-4
	12.70[.500]	10.16[.400]	4	10	102536-3
	10.16[.400]	7.62[.300]	3	8	102536-2
	7.62[.300]	5.08[.200]	2	6	102536-1
	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 06MAR09 RAGHAVENDRA		 TE Connectivity			
		CHK 06MAR09 JEFFREY GESFORD					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME COVER—HALF, LOW PROFILE, MT, AMPMODU, .100 C/L			
		0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± 0.13[.005] 4 PLC ± — ANGLES — ± —					
MATERIAL		FINISH					
		WEIGHT —		SIZE A2 CAGE CODE 00779 DRAWING NO. C-102536		RESTRICTED TO —	
CUSTOMER DRAWING				SCALE 5:1		SHEET 1 OF 1	REV H2