

## RJ45 connector - VS-PPC-C1-RJ45-POBK-PG9-4Q5 - 1608126

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



RJ45 connector, IP67, with push-pull interlocking, plastic housing, CAT5e, 4-pos., with QUICKON fast connection technology, for 1-wire and 7-wire conductors AWG 26 ... 22, for cable cross section 5.0 mm ... 8.0 mm



### Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356159968
Weight per Piece (excluding packing)	0.032 kg
Custom tariff number	85366990
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Mechanical characteristics

Standards/specifications	IEC PAS 61076-3-117
Number of positions	4
Connection profile	RJ45 8(4)
Locking type	Push Pull
Shielded	yes
Insertion/withdrawal cycles	≥ 500
Connection method	IDC fast connection
Conductor cross section	0.13 mm <sup>2</sup> ... 0.32 mm <sup>2</sup> (solid) 0.14 mm <sup>2</sup> ... 0.36 mm <sup>2</sup> (flexible)
Connection cross section AWG	26 ... 22 (solid) 26 ... 22 (flexible)
External cable diameter	5 mm ... 8 mm
Cable outlet	straight

# RJ45 connector - VS-PPC-C1-RJ45-POBK-PG9-4Q5 - 1608126

## Technical data

### Mechanical characteristics

Cable structure	1x4xAWG22/7; SF/TQ
Color	black
Degree of protection	IP65/IP67
No. of cable outlets	1
Note	This product corresponds to the PROFINET Cabling and Interconnection Technology Guideline for PROFINET regulations, version 2.00, order no: 2.252, Chapter 8.2 Connectors for Outside Environment (Balanced cabling) and chapter 13 Application specific Cabling and Interconnection Technology (AIDA)

### Ambient conditions

Ambient temperature (operation)	-10 °C ... 60 °C
---------------------------------	------------------

### Material data

Flammability rating according to UL 94	V0
Housing material	PA-GF
Contact carrier material	PC
Contact material	CuSn
Contact surface material	Au/Ni
Material	Plastic
Cable gland material	PA
O-ring material	NBR
Cable seal material	TPE
Material housing intermediate seal	NBR
Outer sheath, material	PVC
Height	30 mm

### Electrical characteristics

Number of positions	4
Nominal voltage $U_N$	48 V
Nominal current $I_N$	1 A
Transmission characteristics (category)	CAT5 (IEC 11801:2002)
GRP transmission properties	CAT5 (IEC 11801:2002) CAT5 (IEC 11801:2002)
Rated current	1.75 A
Overvoltage category	I
Degree of pollution	2
Contact resistance	0.001 $\Omega$ (Wire – IDC)
	0.005 $\Omega$ (Litz wires – IDC)
Rated voltage (III/3)	72 V (DC)

### Standards and Regulations

Standards/regulations	IEC PAS 61076-3-117
Connection in acc. with standard	CUL
Flammability rating according to UL 94	V0

# RJ45 connector - VS-PPC-C1-RJ45-POBK-PG9-4Q5 - 1608126

## Technical data

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260700
eCl@ss 6.0	27260700
eCl@ss 7.0	27440101
eCl@ss 8.0	27440101
eCl@ss 9.0	27440101

### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC001121
ETIM 5.0	EC002636
ETIM 6.0	EC002636
ETIM 7.0	EC002636

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	39121409

## Approvals

### Approvals

---

#### Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

---

#### Ex Approvals

---

### Approval details

# RJ45 connector - VS-PPC-C1-RJ45-POBK-PG9-4Q5 - 1608126

## Approvals

UL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 118976
Nominal voltage UN		50 V	
Nominal current IN		1.75 A	
mm <sup>2</sup> /AWG/kcmil		22	

cUL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 118976
Nominal voltage UN		50 V	
Nominal current IN		1.75 A	
mm <sup>2</sup> /AWG/kcmil		22	

EAC		B.01742
-----	--	---------

cULus Recognized	
------------------	--

## Accessories

### Accessories

Stripping tool - VS-CABLE-STRIP-VARIO - 1657407

Stripping tool, for the multi-level stripping of shielded cables

