





MATERIAL NUMBER	OLD PART NUMBER	FINISHED LENGTH
130013-0229	1R3006A24A120	12.00" +1.75" -0 [1.3M +44.5 -0]
130013-0233	1R3006A24F030	3.00' +2.19" -0 [.9M +55.6 -0]
130013-0235	1R3006A24F060	6.00' +3.50" -0 [1.8M +88.9 -0]



MALE FACE VIEW

1	GREEN
2	RED WITH #2
3	RED WITH #3

WIRING DIAGRAM



KNOCKOUT HOLE

VOLTAGE RATING	600 VAC/VDC
AMPERAGE RATING	13 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-20°C TO 105°C
UL CERTIFICATIONS	UL LISTED, FILE NO. E258922
CSA CERTIFICATIONS	CSA CERTIFIED, FILE NO. LR6837

ITEM	COMPONENT	MATERIAL	FINISH
1	INSERT	PVC	YELLOW
2	CONTACT PIN	COPPER ALLOY	GOLD OVER NICKEL
3	RECEPTACLE SHELL	ZINC DIE CAST	BLACK E-COATED
4	CONDUCTOR - 16 AWG. 26 x #30 COPPER STRANDING, 600V	PVC	SEE WIRING DIAGRAM
5	FLAG LABEL	PLASTIC FILM	BLACK/YELLOW

RLSD DRAWING EC NO: WNA2010-0425 DRWN: BWOODMAN2010/01/06 CH'KD: TW APPR: JFMURPHY 2010/01/14 A	DESCRIPTION REV	QUALITY SYMBOL ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 1:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY	DATE	TITLE				
			4 PLACES	±---	±---	----	----	MINI-CHANGE RECEPTACLE 3 POLE MALE 1/2 NPT US AUTO CODE				
			3 PLACES	±---	±.005	CHECKED BY	DATE					
			2 PLACES	±0.13	±.010	TW	2010/01/07					
			1 PLACE	±0.25	±.020	APPROVED BY	DATE					
			ANGULAR ±1/2°			JFMURPHY	2010/01/14	molex		MOLEX INCORPORATED		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO. SEE CHART		DOCUMENT NO. SD-130013-013		SHEET NO. 1 OF 1		
						SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					