


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		C	REVISED PER 0G3B-0326-01	23JUL2001	EZ	DB
			D	REVISED EC 0G3B-0191-03	30APR2003	SW	CR

0.5
TYP

POLARIZATION KEY SLOT

INTERLOCKING
FEATURE

CLAMPING SCREW



282807-3 AS SHOWN

1

2

3

4

5

6

7

MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
CLAMP: BRASS, NICKEL PLATED.
CONTACT SPRING: PHOSPHOR BRONZE, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.

2. END-TO-END STACKABLE W/INTERLOCK WITHOUT LOSS OF CENTERLINE SPACING.

3. WIRE SIZE RANGE
SOLID WIRE: 0,03-2,5mm (13 AWG).
STRANDED WIRE: 0,03-1,5mm (15 AWG).

4. RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.FILE N° E60677

5. IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.

6. NOT CUMULATIVE TOLERANCE.

7. CHARACTERS INK STAMPED WHITE.

A

15.5

RETENTION LATCH

MATING FACE

18.4

DETAIL Z

1

2

3

7

2.54 REF

2.54 REF

5.08±0.05
TYP

6

DETAIL Z	15.24	3	282807-5
-	20.32	4	282807-4
-	15.24	3	282807-3
-	10.16	2	282807-2
MARKING	L	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN E. ZANOLINI 23JUL2001	Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK D. BIEVENOUR 23JUL2001	NAME TERMINAL BLOCK PLUG STACKING W/INTERLOCK, 5.08mm PITCH	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.2 1 PLC ±.25 2 PLC ±.25 3 PLC ±.25 4 PLC ±.25 ANGLES ±2 FINISH		APVD D. BIEVENOUR 23JUL2001	SIZE A2	
MATERIAL		PRODUCT SPEC 108-20166	CAGE CODE 00779	
		APPLICATION SPEC 114-20079	DRAWING NO C-282807	
		WEIGHT -	RESTRICTED TO -	
		CUSTOMER DRAWING	SCALE 3:1	
			SHEET 1	
			OF 1	
			REV D	