




Low profile transformer FL 24/12

Type		FL 24/12
Electrical data	Input	
	Rated input Voltage	2 x 115 Vac
	Rated frequency	50 - 60 Hz
	Output	
	Rated output voltage	2 x 12 Vac
	Rated Power	24.0 VA
	No-load voltage (app. x factor)	1.20
	No-load loss (typ.)	1.60 W
	Efficiency	77 %
	Standards	
	Classification	Safety isolating transformer
	Approvals	
	Approvals	cURus, ENEC 10 (VDE)
	Environment	
	Ambient temperature max.	40 °C
Safety and protection		
Type	encapsulated	
Class of Insulation System	VDE=E, UL=class 105	
Protection index	IP 00	
Safety class (prepared)	II	
Short circuit strength	non-short-circuit proof	
Order numbers		
Order Number	FL 24/12	

Type		FL 24/12
Terminal and mounting		
Terminals		Pins for printed circuit boards
Measures and weights		
Core type		UI 39/17
Weight		0.45 kg

30
Mechanical data



Subjects to change.