





D



C



B



A

RECOMMENDED HOLE LAYOUT
TOLERANCE ±.002 UNLESS OTHERWISE NOTED

SPECIFICATIONS:
BREAK-BEFORE-MAKE

MATERIAL:
SLIDER, GLASS FILLED NYLON, UL94-HB, BLACK.
BASE, GLASS FILLED PBT, BLUE.
COVER, GLASS FILLED PBT, BLUE.
SLIDE PLATE, STAINLESS STEEL.
ACTUATOR, PPS, BLACK.
ROCKER CONTACT(GOLD), COPPER ALLOY, GOLD OVER NICKEL PLATING.
ROCKER CONTACT(SILVER), COPPER ALLOY PLUS COINED SILVER.
FIXED CONTACT/TERMINAL (GOLD), COPPER ALLOY, GOLD OVER NICKEL PLATE.
FIXED CONTACT/TERMINAL(SILVER), COPPER ALLOY PLUS COINED SILVER, GOLD OVER NICKEL PLATE.

ELECTRICAL:
CONTACT RATING(SILVER)-3A@115V AC OR 1.5A@230V AC
CONTACT RATING(GOLD)-.4VA MAX@20V DC OR PEAK AC
INITIAL CONTACT RESISTANCE-20 MILLIOHMS MAX.
INSULATION RESISTANCE-1,000 MEGOHMS MIN @ 500V DC
DIELECTRIC STRENGTH- 500 V RMS @ SEA LEVEL.
LIFE EXPECTANCY- 30,000 OPERATIONS.

MECHANICAL:
OPERATING FORCE- 600+/-300 GRAMS.
TRAVEL-.120

ENVIRONMENTAL:
OPERATING TEMPERATURE- -20°C TO +65°C
STORAGE TEMPERATURE- -40°C TO +100°C
SOLDER HEAT RESISTANCE- PER 109-202 CONDITION B.
SOLDERABILITY PER EIA 364-52, CLASS 2, CATAGORY 1.

2,1 & 5,4	NONE	2,3 & 5,6	DPDT	SILVER	MSSA214N04	5-1437580-2
2,1 & 5,4	OFF	2,3 & 5,6	DPDT	GOLD	MSSA211PG04	5-1437580-1
2,1 & 5,4	NONE	2,3 & 5,6	DPDT	GOLD	MSSA211NGRA04	5-1437580-0
2,1 & 5,4	NONE	2,3 & 5,6	DPDT	GOLD	MSSA211NG04	4-1437580-9
			TYPE	PLATING	ALCO PART NO.	PART NO.
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN R BROWN 20APR04	TE Connectivity	
DIMENSIONS: INCHES				CHK M SARVER 20APR04		
				APVD M SARVER 20APR04	NAME SLIDE SWITCH, DP (MSS-211 & 214)	
				PRODUCT SPEC		
MATERIAL -				APPLICATION SPEC	SIZE A2	RESTRICTED TO -
				WEIGHT -	CAGE CODE 00779	
FINISH -				CUSTOMER DRAWING	DRAWING NO C-4-1437580-9	
				SCALE 4:1	SHEET 1 of 1	REV C2