


2 PART EXTENSION LADDERS



Manufactured from distinctive yellow 85mm x 31mm glass fibre channel with heavy duty round aluminium rungs fitted at 250mm centres and swagged over.

The special rung joint, which is keyed into two retaining washers and the stiles, gives a very strong anti twist fixing. Special stay brackets are fitted to give added strength and prevent side sway. The ladder sections interlock and both push up and rope operated types have AUTO CLUTCH MECHANISM. The clutch is an aluminium proven design that has been developed over many years and will arrest itself rung by rung. Anti chafing during extension is achieved by fitting special rubber blocks into the channel section ends. Wall running wheels are fitted to all ladders to eliminate wear.

THIS PRODUCT COMPLIES TO: ANSI 14-5 and ESI 13-1.

2 SECTION EXTENDING LADDERS PUSH-UP

CODE NO.	LENGTH CLOSED	LENGTH EXTENDED	RUNGS PER SECTION
GL2 09	2.35m	4.05m	9
GL2 12	3.05m	5.55m	12
GL2 14	3.55m	6.30m	14
GL2 16	4.10m	7.55m	16
GL2 19	4.83m	8.85m	19