



On-Site Guide (BS 7671:2008 Wiring Regulations, incorporating Amendment No 1:2011)

Author: IET Publications (edited by Mark Coles)

Book details

Author: IET Publications (edited by Mark Coles)

Year: 2011

Format: Paperback, wire-bound

Pages: 196

ISBN: 978-1-84919-287-3

Stock status: In stock

Product code: PWGO171B

Who is this book for: Essential for all electricians, electrical contractors, installation designers, and students in further education and professional training.

Product description

The On-Site Guide is an essential guide for quick reference of information on BS 7671 (The IET Wiring Regulations) the national standard to which all domestic and industrial wiring must conform. The Guide has been revised to align with the 17th Edition Amendment No 1.

Contents

Cooperating organisations	6
Preface	7
Foreword	9
Section 1 Introduction	11
1.1 Scope	11
1.2 Building Regulations	12
1.3 Basic information required	14
Section 2 The electrical supply	15
2.1 General layout of equipment	15
2.2 Function of components	17
2.3 Separation of gas installation pipework from other services	18
2.4 Portable generators	19
Section 3 Protection	23
3.1 Types of protective device	23
3.2 Overload protection	23
3.3 Fault current protection	23
3.4 Protection against electric shock	24
3.5 Automatic disconnection	25
3.6 Residual current devices (RCDs)	26
3.7 Surge protective devices (SPDs)	31
Section 4 Earthing and bonding	39
4.1 Protective earthing	39
4.2 Legal requirements	39
4.3 Main protective bonding of metallic services	39
4.4 Earthing conductor and main protective bonding conductor cross-sectional areas	40
4.5 Main protective bonding of plastic services	41
4.6 Supplementary equipotential bonding	42
4.7 Additional protection – supplementary equipotential bonding	42
4.8 Supplementary bonding of plastic pipe installations	43
4.9 Earth electrode	43
4.10 Types of earth electrode	43
4.11 Typical earthing arrangements for various types of earthing system	44

Section 5	Isolation and switching	45
5.1	Isolation	45
5.2	Switching off for mechanical maintenance	46
5.3	Emergency switching	46
5.4	Functional switching	47
5.5	Firefighter's switch	47
Section 6	Labelling	49
6.1	Additional protection	49
6.2	Retention of a dangerous electrical charge	49
6.3	Where the operator cannot observe the operation of switchgear and controlgear	49
6.4	Unexpected presence of nominal voltage exceeding 230 V	49
6.5	Connection of earthing and bonding conductors	50
6.6	Purpose of switchgear and controlgear	50
6.7	Identification of protective devices	50
6.8	Identification of isolators	50
6.9	Isolation requiring more than one device	50
6.10	Periodic inspection and testing	51
6.11	Diagrams	51
6.12	Residual current devices	51
6.13	Warning notice – non-standard colours	52
6.14	Warning notice – alternative supplies	52
6.15	Warning notice – high protective conductor current	53
6.16	Warning notice – photovoltaic systems	54
Section 7	Final circuits	55
7.1	Final circuits	55
7.2	Standard final circuits	68
7.3	Installation considerations	73
7.4	Proximity to electrical and other services	75
7.5	Earthing requirements for the installation of equipment having high protective conductor current	77
7.6	Electrical supplies to furniture	79
Section 8	Locations containing a bath or shower	81
8.1	Summary of requirements	81
8.2	Shower cubicle in a room used for other purposes	84
8.3	Underfloor heating systems	84
Section 9	Inspection and testing	85
9.1	Inspection and testing	85
9.2	Inspection	85
9.3	Testing	87
Section 10	Guidance on initial testing of installations	89
10.1	Safety and equipment	89
10.2	Sequence of tests	90
10.3	Test procedures	90
Section 11	Operation of RCDs	105
11.1	General test procedure	106
11.2	General-purpose RCCBs to BS 4293	106

11.3	General-purpose RCCBs to BS EN 61008 or RCOs to BS EN 61009	106
11.4	RCD protected socket-outlets to BS 7288	106
11.5	Additional protection	106
11.6	Integral test device	107
11.7	Multipole RCDs	107
Appendix A	Maximum demand and diversity	109
Appendix B	Maximum permissible measured earth fault loop impedance	113
Appendix C	Selection of types of cable for particular uses and external influences	121
Appendix D	Methods of support for cables, conductors and wiring systems	127
Appendix E	Cable capacities of conduit and trunking	133
Appendix F	Current-carrying capacities and voltage drop for copper conductors	139
Appendix G	Certification and reporting	151
G1	Introduction	151
G2	Certification	151
G3	Reporting	152
G4	Introduction to Model Forms from BS 7671:2008(2011)	153
Appendix H	Standard circuit arrangements for household and similar installations	173
H1	Introduction	173
H2	Final circuits using socket-outlets complying with BS 1363-2 and fused connection units complying with BS 1363-4	173
H3	Radial final circuits using 16 A socket-outlets complying with BS EN 60309-2 (BS 4343)	176
H4	Cooker circuits in household and similar premises	176
H5	Water and space heating	177
H6	Height of switches, socket-outlets and controls	177
H7	Number of socket-outlets	178
Appendix I	Resistance of copper and aluminium conductors	181
Appendix J	Selection of devices for isolation and switching	185
Appendix K	Identification of conductors	187
K1	Introduction	187
K2	Addition or alteration to an existing installation	189
K3	Switch wires in a new installation or an addition or alteration to an existing installation	189
K4	Intermediate and two-way switch wires in a new installation or an addition or alteration to an existing installation	190
K5	Line conductors in a new installation or an addition or alteration to an existing installation	190
K6	Changes to cable core colour identification	190
K7	Addition or alteration to a d.c. installation	191
Index		193