



LOC		DIST		REVISIONS					
FT		0		P	LTR	DESCRIPTION	DATE	DWN	APVD
				P1		REVISED PER ECO-06-831	1/13/06	SS	GS



- WILL ACCEPT (12) MULTIMATE AND (4) TYPE XII PIN CONTACTS.
 - CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
 - NO. 4 FASTENERS RECOMMENDED FOR MOUNTING.
 - THIS CONNECTOR WILL ACCEPT INSULATION DIAMETERS UP TO 3.81 [.150].
- HOUSING: NYLON, BLACK.
- PERIPHERAL SEAL: ELASTOMER, GRAY.
- PERMANENT WHITE MARKED OR WHITE INK STAMPED CAVITY IDENTIFICATION.
- HOUSING: NYLON, RED.
- PERIPHERAL SEAL: ELASTOMER, GRAY.
- WHITE DOT NEAR POSITION 1 ON WIRE ENTRY FACE.

PRELIMINARY	8	—	YES	A	1-207486-1
PRELIMINARY	6	—	YES	A	207486-9
	6	—	YES	A	207486-7
	6	4	YES	A	207486-6
	5	—	YES	A	207486-5
	6	—	NO	B	207486-2
	5	—	NO	A	207486-1
NOTES		THREADED INSERTS	PERIPHERAL SEAL	SEE DETAIL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. BINNER	05/26/94	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		CHK R. STONE	6-23-94	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-10024		RECEPTACLE HOUSING, STANDARD SEX, SHELL SIZE 23, CPC	
0 PLC ± -		APPLICATION SPEC		SIZE CAGE CODE DRAWING NO	
1 PLC ± -		—		RESTRICTED TO	
2 PLC ± 0.13 [.005]		—		A1 00779	
3 PLC ± -		—		©=207486	
4 PLC ± -		—		CUSTOMER DRAWING	
ANGLES ± -		—		SCALE 2:1	
FINISH —		—		SHEET 1 OF 1	
—		—		REV P1	