

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [45830-0227](#)
Status: **Active**
Overview: HD Mezz™
Description: 1.20mm by 2.00mm Pitch HD Mezz™ Plug, 351 Circuits, 8.00mm Unmated Height, 27 Rows, Tin (Sn) Plating

Documents:

[3D Model](#) [Test Summary TS-45830-9003 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-45802-001 \(PDF\)](#)

Agency Certification


CSA LR19980

General

Product Family PCB Headers
 Series [45830](#)
 Application Board-to-Board, Signal
 Comments 1.20mm Pitch Pin-to-Pin and 2.00mm Pitch Row-to-Row
 Overview [HD Mezz™](#)
 Product Name HD Mezz™
 UPC 800756957982

Physical

Breakaway No
 Circuits (Loaded) 351
 Circuits (maximum) 351
 Color - Resin Black
 Durability (mating cycles max) 100
 First Mate / Last Break No
 Flammability 94V-0
 Glow-Wire Compliant No
 Guide to Mating Part No
 Keying to Mating Part None
 Lock to Mating Part Yes
 Material - Metal High Performance Alloy (HPA)
 Material - Plating Mating Gold
 Material - Plating Termination Tin
 Material - Resin High Temperature Thermoplastic
 Net Weight 14.377/g
 Number of Rows 27
 Orientation Vertical
 PCB Locator Yes
 PCB Retention Yes
 Packaging Type Tray
 Pitch - Mating Interface 1.20mm
 Pitch - Termination Interface 1.20mm
 Plating min - Mating 0.762µm
 Plating min - Termination 2.540µm
 Polarized to Mating Part Yes
 Polarized to PCB Yes
 Robotic Placement Vacuum Pick-Up Clip
 Shrouded Closed Ends
 Stackable No
 Surface Mount Compatible (SMC) Yes
 Temperature Range - Operating -55°C to +105°C



EU RoHS

ELV and RoHS Compliant
REACH SVHC
 Not Reviewed
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[45830Series](#)

Mates With

[45802 HD Mezz™ Receptacle](#)

Termination Interface: Style Surface Mount
Unmated Height 8.00mm

Electrical

Current - Maximum per Contact 2A
Voltage - Maximum 250V AC

Solder Process Data

Duration at Max. Process Temperature (seconds) 20
Lead-free Process Capability Reflow Capable (SMT only)
Max. Cycles at Max. Process Temperature 2
Process Temperature max. C 260

Material Info

Reference - Drawing Numbers

Product Specification PS-45802-001
Sales Drawing SD-45830-0001, SD-45830-0002
Test Summary TS-45830-9003

This document was generated on 01/21/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION