



## Main

|                             |   |
|-----------------------------|---|
| Range                       | Spacial   |
| Product name                | Spacial CRN                                       |
| Device application          | Multi-purpose                                     |
| Product or component-type   | Compact enclosure                                 |
| Enclosure nominal-height    | 500 mm  |
| Enclosure nominal width     | 400 mm  |
| Enclosure nominal depth     | 150 mm  |
| Installation accessory-type | Wall-mounting                                     |
| Device composition          | Lock 1<br>Door 1<br>Body 1<br>Cable gland plate 1 |
| Door type                   | Plain   |
| Mounting plate description  | Without mounting plate                            |


## Complementary

|                             |  |
|-----------------------------|--|
| Variant particularity       | Sides made from a single folded section<br>Back welded with double profile forming a protected sealed area |
| Number of doors             | 1 front face   |
| Door opening side           | Reversible 120 °   |
| Lock type                   | 3 mm double-bar lock   |
| Type of gland plate         | Standard   |
| Accessibility for operation | Front  |
| Removable parts             | Door by hinges<br>Cable gland plate by screws  |
| Material                    | Steel for body   |
| Surface finish              | Epoxy-polyester powder   |
| Colour                      | Grey RAL 7035  |
| Standards                   | IEC 62208  |
| Product certifications      | UL<br>CUL  |

## Environment

|                         |                              |
|-------------------------|------------------------------|
| IP degree of protection | IP66 conforming to IEC 60529 |
| IK degree of protection | IK10 conforming to IEC 62262 |

## Offer Sustainability

|                                  |  |
|----------------------------------|--|
| Sustainable offer status         | Green Premium product  |
| RoHS (date code: YYWW)           | Compliant - since 0940 - Schneider Electric declaration of conformity  <a href="#">Schneider Electric declaration of conformity</a> |
| REACH                            | Reference not containing SVHC above the threshold  |
| Product environmental profile    | Available  |
| Product end of life instructions | Need no specific recycling operations  |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

### Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

|                       |                |
|-----------------------|----------------|
| Product Life Status : | Commercialised |
|-----------------------|----------------|