


















- Standard hood
- Corrosion-resistant hood (series K)



Locking bayonet on hood

Style	Ordering number	Cable entry			Description	Outline drawing dimensions in mm	
Hood side entry standard construction 							
		PG	PG	PG			
	41.32.32.07 41.32.32.80 41.32.32.70	21	21	21	HA.32.STS.1.21 HA.32.STS.1.21.Z HA.32.STS.1.21.G		
	51.41.32.32.07 51.41.32.32.80 51.41.32.32.70	21	21	21	HA-K.32.STS.1.21 HA-K.32.STS.1.21.Z HA-K.32.STS.1.21.G		
high construction 	49.32.50.07 49.32.50.80 49.32.50.70 49.32.50.09 49.32.50.81 49.32.50.71	21 29 29	21 21 29	21 21 29	HD.50.STS.1.21 HD.50.STS.1.21.Z HD.50.STS.1.21.G HD.50.STS.1.29 HD.50.STS.1.29.Z HD.50.STS.1.29.G		
	51.49.32.50.07 51.49.32.50.80 51.49.32.50.70 51.49.32.50.09 51.49.32.50.81 51.49.32.50.71	21 29 29	21 21 29	21 21 29	HD-K.50.STS.1.21 HD-K.50.STS.1.21.Z HD-K.50.STS.1.21.G HD-K.50.STS.1.29 HD-K.50.STS.1.29.Z HD-K.50.STS.1.29.G		
top entry standard construction 	41.30.32.07 41.30.32.80 41.30.32.70	21	21	21	HA.32.STO.1.21 HA.32.STO.1.21.Z HA.32.STO.1.21.G		
	51.41.30.32.07 51.41.30.32.80 51.41.30.32.70	21	21	21	HA-K.32.STO.1.21 HA-K.32.STO.1.21.Z HA-K.32.STO.1.21.G		
high construction 	49.30.50.07 49.30.50.80 49.30.50.70 49.30.50.09 49.30.50.81 49.30.50.71	21 29 29	21 21 29	21 21 29	HD.50.STO.1.21 HD.50.STO.1.21.Z HD.50.STO.1.21.G HD.50.STO.1.29 HD.50.STO.1.29.Z HD.50.STO.1.29.G		
	51.49.30.50.07 51.49.30.50.80 51.49.30.50.70 51.49.30.50.09 51.49.30.50.81 51.49.30.50.71	21 29 29	21 21 29	21 21 29	HD-K.50.STO.1.21 HD-K.50.STO.1.21.Z HD-K.50.STO.1.21.G HD-K.50.STO.1.29 HD-K.50.STO.1.29.Z HD-K.50.STO.1.29.G	