






Technical drawing of a mechanical component, likely a connector or switch, showing dimensions and features:

- Overall width: 13,8
- Top hole diameter: $\phi 2,6$
- Right side hole diameter: 5,2
- Bottom hole diameter: 7,4
- Bottom hole diameter (left): 50
- Bottom hole diameter (right): 1st contact
- Bottom hole diameter (center): Min. 4,1
- Max. 6,5 (overall length)

				Dat.	Name	 All Dim. in mm Orig. Size DIN A 3	SEK 18 Male Connector Standard		Maßstab/ Scale
34890	01/02/08	PK	Detail.	01/12/99	JB		50 poles		1,5:1
29753	11/03/02	JB	Insp.				Angled pins		
29739	03/12/01	JB	Stand.				Short locking levers		
27931	15/06/00	JB	HARTING EURL F-95972 Paris					TB 09 18 550 X91X	Blatt/ Page 2 / 2
26554	01/12/99	JB							
Mod.	Dat.	Name					Sub.		