


LEDs & INDICATORS

515 MPA Series

- Threaded body for panel thicknesses 0.5-3.5mm, panel cut-out 6.4mm diameter
- Stripped wire termination 164mm long, PVC
- LED, Filament 6-28V 30-40mA and Neons 125-240V 0.8-1mA, as standard
- Polycarbonate lens/body, chrome bezel, supplied with nut and shakeproof washer
- Red, green, amber, clear, blue and opal lens colour options as standard
- Maximum working temperature 105°C
- Custom wire lengths and specification to order



	TYPE NO.	515	1	05 - XXXX - T / XXX
515 Series Indicator		515		
Lens Type	Trapezoid	1		
	Top Hat	2		
Stripped wire 164mm long				05
LED, black cathode & white anode wires				LED
Filament 6V 40mA, white wire				640
Filament 12V 35mA, yellow wire				1235
Filament 14V 40mA, yellow wire				1440
Filament 24V 35mA, green wire				24
Filament 28V 30mA, green wire				28
Neon 125V 1mA, blue wire				125
Neon 240V 0.8mA, red wire				240
Transparent lens				T
Lens colour Red				RED
Lens colour Green				GRN
Lens colour Amber				AMB
Lens colour Clear				CLR
Lens colour Blue				BLU
Lens colour Opal				OPL

Body Dimensions

