





| LOC |  | DIST |  | REVISIONS |     |                           |  |  |           |     |      |
|-----|--|------|--|-----------|-----|---------------------------|--|--|-----------|-----|------|
| BV  |  | 00   |  | P         | LTR | DESCRIPTION               |  |  | DATE      | DWN | APVD |
|     |  |      |  |           | C5  | REVISED PER ECO-11-005030 |  |  | 11MAR2011 | RK  | HMR  |
|     |  |      |  |           |     |                           |  |  |           |     |      |
|     |  |      |  |           |     |                           |  |  |           |     |      |
|     |  |      |  |           |     |                           |  |  |           |     |      |
|     |  |      |  |           |     |                           |  |  |           |     |      |



- 1 ACCEPTS #4 SELF TAPPING THREAD CUTTING SCREWS OR METRIC EQUIVALENT. DRIVE TO 0.6 N-m MAX
- 2 DATE CODE IN THIS LOCATION USING 5 DIGIT CODE FIRST 2 DIGITS = YEAR, SECOND 2 DIGITS = WEEK LAST DIGIT = DAY.
- 3 MATERIALS: HEADER HOUSING - GLASS FILLED PBT PINS - TIN OR GOLD PLATED BRASS GASKET - SILICONE
- 4 HOUSING COLORS ARE MECHANICALLY KEYED TO MATE ONLY WITH IDENTICALLY COLORED PLUG ASSEMBLIES.
- 5. HEADER MATES TO PLUG ASSEMBLY 770680 WHICH USES REELED TERMINAL 770520 OR LOOSE PIECE TERMINAL 770854




776228-1 & 1-776228-1 SHOWN


|                |          |                     |
|----------------|----------|---------------------|
| BLUE           | DURAGOLD | 1-776228-5          |
| GRAY           | DURAGOLD | 1-776228-4          |
| NATURAL        | DURAGOLD | 1-776228-2          |
| BLACK          | DURAGOLD | 1-776228-1          |
| BLUE           | TIN      | 776228-5            |
| GRAY           | TIN      | 776228-4            |
| NATURAL        | TIN      | 776228-2            |
| BLACK          | TIN      | 776228-1            |
| HEADER COLOR 4 |          | PLATING PART NUMBER |

|                                        |  |                             |                               |  |
|----------------------------------------|--|-----------------------------|-------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN D. STRAUSSER 05MAR2010  | NAME                          |  |
| DIMENSIONS:                            |  | CHK D. STRAUSSER 22MAR2010  | PRODUCT SPEC                  |  |
| mm                                     |  | APVD D. STRAUSSER 27APR2010 | APPLICATION SPEC              |  |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: |  | 108-1329                    | SIZE CAGE CODE DRAWING NO     |  |
| 9 PLC ±.2                              |  | 114-16016                   | RESTRICTED TO                 |  |
| 1 PLC ±0.13                            |  | WEIGHT -                    | A100779C-776228               |  |
| 3 PLC ±.1                              |  | CUSTOMER DRAWING            | SCALE 4:1 SHEET 1 OF 2 REV C5 |  |
| 4 PLC ±.1                              |  |                             |                               |  |
| ANGLES ±4°                             |  |                             |                               |  |
| FINISH                                 |  |                             |                               |  |


| LOC | DIST | REVISIONS |     |             |      |
|-----|------|-----------|-----|-------------|------|
| BV  | 00   | P         | LTR | DESCRIPTION | DATE |
|     |      | -         | -   | SEE SHEET 1 | -    |
|     |      |           |     |             |      |
|     |      |           |     |             |      |
|     |      |           |     |             |      |
|     |      |           |     |             |      |
|     |      |           |     |             |      |




RECOMMENDED P.C. BOARD LAYOUT  
FOR 1.57 THICK P.C. BOARD




RECOMMENDED MOUNTING HOLE LAYOUT  
FOR 5.0 MAX THICK PANEL




SECTION A-A  
OPTIONAL CONSTRUCTION IF PANEL  
THICKNESS IS GREATER THAN 2.0




SECTION A-A  
OPTIONAL CONSTRUCTION IF PANEL  
THICKNESS IS GREATER THAN 2.0




KEYING FOR 776228-1 AND 776228-5  
SCALE 2:1




KEYING FOR 776228-2 AND 776228-4  
SCALE 2:1



776228-2 & 1-776228-2  
KEY LOCATION  
SCALE 2:1



776228-4 & 1-776228-4  
KEY LOCATION  
SCALE 2:1



776228-5 & 1-776228-5  
KEY LOCATION  
SCALE 2:1

|                                        |  |                                   |                               |  |
|----------------------------------------|--|-----------------------------------|-------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN<br>D. STRAUSSER<br>05MAR2010  | TE Connectivity               |  |
| DIMENSIONS:                            |  | CHK<br>D. STRAUSSER<br>22MAR2010  | NAME                          |  |
| mm                                     |  | APVD<br>D. STRAUSSER<br>27APR2010 | PRODUCT SPEC                  |  |
|                                        |  |                                   | 108-1329                      |  |
|                                        |  |                                   | APPLICATION SPEC              |  |
|                                        |  |                                   | 114-16016                     |  |
|                                        |  |                                   | WEIGHT                        |  |
|                                        |  |                                   | CUSTOMER DRAWING              |  |
|                                        |  |                                   | SCALE 2:1 SHEET 2 OF 2 REV C5 |  |