

Technic 420

DESCRIPTION AND GENERAL PROPERTIES

- **Material** Neoprene and natural latex
- **Length (cm)** 31
- **Thickness (mm)** 0.75
- **Wrist** Straight cuff
- **Colour/Color** Black
- **Interior finish** Flocked
- **Exterior finish** Embossed texture
- **Size / EAN** 6 7 8 9 10
- **Packaging** 1 pair/bag - 10 pairs/box - 100 pairs/carton



PERFORMANCE RESULTS

Certification category 3

CE 0334



AJKL


3121

Legends



MECHANICAL HAZARDS EN 388

PERFORMANCE LEVELS



LOW CHEMICAL PROTECTION EN 374



MICRO-ORGANISMS EN 374




RADIOACTIVE CONTAMINATION EN 421



HEAT AND FIRE EN 407

PERFORMANCE LEVELS




SPECIFIC CHEMICAL PROTECTION EN 374

Letter Code	Chemical product
A	Methanol
B	Acetone
C	Acetonitrile
D	Dichloromethane
E	Carbon Disulfide
F	Toluene
G	Diethylamine
H	Tetrahydrofurane
I	Ethyl acetate
J	n-Heptane
K	Sodium hydroxide 40%
L	Sulphuric acid 96%



COLD HAZARDS EN 511

PERFORMANCE LEVELS



For more details: www.mapa-pro.com

SPECIFIC ADVANTAGES

- Freedom of movement, due to the supple quality of the neoprene and the comfort of the cotton flock-lining
- Good grip, due to embossed texture

MAIN FIELDS OF USE

Automotive/mechanical industry

- Electric accumulator and battery manufacturing

Chemical industry

- Handling, loading and unloading of chemicals

Other industries

- Spreading fertilizer
- Preparation of industrial glues
- Industrial cleaning, maintenance

INSTRUCTIONS FOR USE

Instructions for use

- It is recommended to check that the gloves are suitable for the intended use, because the conditions of use at workplace may differ from the «CE»-type tests.
- It is not recommended for persons sensitized to natural latex, thiazoles and dithiocarbamates to use these gloves.
- Put the gloves on dry, clean hands.
- Do not use the gloves in contact with a chemical for a duration in excess of the measured breakthrough time. Refer to the website www.mapa-pro.com or contact the Technical Customer Service - MAPA PROFESSIONNEL (stc.mapaspontex@mapaspontex.fr) in order to know this breakthrough time. Use 2 pairs alternatively when in long duration contact with a solvent.
- Turn the cuff end down in order to prevent a hazardous chemical from dripping onto the arm.
- Inspect the gloves for cracks or snags before reusing them.

Storage conditions

Store the gloves in their original packaging at a temperature not below 5°C.

Laundering conditions

Before taking off the gloves, clean them as appropriate :

- in use with paints, pigments and inks : wipe with a clean cloth dampened with a suitable solvent, and rub over with a dry cloth
 - in use with a solvent (dilutents, etc...) : rub over with a dry cloth
 - in use with acids or alkalies : thoroughly rinse the gloves under running water, and rub over with a dry cloth
- Caution : improper use of the gloves or submitting them to a cleaning or laundering process which is not specifically recommended can alter their performance levels.

Drying conditions

Ensure the inside of the gloves is dry before putting them on again.

LEGISLATION

This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council. This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).

- CE-Type Examination Certificate

0072/014/162/05/94/10514

- Issued by the notified body nr

0072

I.F.T.H. – Av. Guy de Collongue - F-69134 ECULLY CEDEX

- Quality assurance certificat

0334 Asqual 14 rue des Reculettes -F-75013 PARIS