



C-CLAMP LOCKING PLIERS

PART NO.	SIZE INCH	L MM	T MM	a MM			G.W. (kg)
71601	11"	273	14.5	144	6	36	20.0
71601-S	11"	288	30.0	144	6	36	20.0



CHAIN CLAMP LOCKING PLIERS


PART NO.	SIZE INCH	L MM	a MM			G.W. (kg)
71701	19"	714	66	6	36	26.0



SNAP RING - EXTERNAL OPEN STRAIGHT

PART NO.	SIZE INCH	L MM	CAPACITY			G.W. (kg)
72001	7"	175	10-40	6	90	13.4


- Made of alloy steel with heating treatment
- Black finish surface prevents rusty



SNAP RING - EXTERNAL OPEN CURVED

PART NO.	SIZE INCH	L MM	CAPACITY			G.W. (kg)
72002	7"	175	10-40	6	90	13.4


- Made of alloy steel with heating treatment
- Black finish surface prevents rusty



SNAP RING - INTERNAL CLOSE STRAIGHT

PART NO.	SIZE INCH	L MM	CAPACITY			G.W. (kg)
72004	7"	175	12-65	6	90	13.4


- Made of alloy steel with heating treatment
- Black finish surface prevents rusty



SNAP RING - EXTERNAL CLOSE CURVED

PART NO.	SIZE INCH	L MM	CAPACITY			G.W. (kg)
72005	7"	175	10-40	6	90	13.4

- Made of alloy steel with heating treatment
- Black finish surface prevents rusty



GERMAN TYPE SNAP RING PLIERS EXTERNAL OPEN STRAIGHT New

PART NO.	SIZE INCH	L MM	CAPACITY			G.W. (kg)
72011	5"	125	8-25	6	36	5.0
72012	7"	175	19-60	6	36	8.0
72013	9"	225	35-100	6	36	12.0
72014	13"	325	85-165	6	36	22.0

- Made of alloy steel with heating treatment
- Black finish surface prevents rusty



GERMAN TYPE SNAP RING PLIERS EXTERNAL OPEN CURVED New

PART NO.	SIZE INCH	L MM	CAPACITY			G.W. (kg)
72021	5"	125	8-25	6	36	5.0
72022	7"	175	19-60	6	36	8.0
72023	9"	225	35-100	6	36	12.0
72024	13"	325	85-165	6	36	22.0

- Made of alloy steel with heating treatment
- Black finish surface prevents rusty

