


# Screwdrivers



## The power is where you put it with the **SK DRALL** screwdriver series

The efficiency with which you use a screwdriver in your daily work, and the safety with which you work, depend to a large extent on the quality of the tool. It is not just the use of high-grade materials but also the shape that matters – in particular the shape of the handles – if you want to stay in control.

STAHLWILLE's **SK DRALL** screwdrivers unite these positive qualities in a manner which is close to perfect. The result is a longlife, ergonomically designed tool providing easy working combined with maximum force transmission – even with greasy hands.



**SK DRALL** screwdrivers are available in sets conveniently positioned in plastic inlays or TCS safety inlays, designed for use with STAHLWILLE Tool Trolleys and Tool Boxes.

### **SK DRALL** handles are made up of 3 components:

#### **1<sup>st</sup> component**

Extremely resistant, impact-safe core made of black polypropylene (PP).

#### **2<sup>nd</sup> component**

Soft, heat-bonded inlay made of easy-to-grip thermoplastic elastomer (TPE).

#### **3<sup>rd</sup> component**

Two large surfaces coated with special fibres, resistant long-term to solvents to improve force transmission and work safety.



Together, these features make the **SK DRALL** tools very pleasant to handle and prevent your hands from slipping off the handles or twisting, even if your hands are damp or oily.

### **Blades**



Made of high-grade Chrome Alloy Steel. Through-hardened. Anchored firmly in the haft due to the extra-wide, forged tang. High resistance to bending.



### **Additional Tommy-bar hole**

When things get really tough, the additional Tommy-bar hole will cope with a fair amount of torque.



The ergonomically designed, almost square handle shape gives maximum contact with the handle, maximum leverage and, as a result, maximum non-slip force transmission, even with oily hands.

## New freedom of choice – DRALL<sup>+</sup> screwdrivers



### 3 handle sizes

The handle sizes for the DRALL<sup>+</sup> screwdrivers are designed specifically to match the drive profiles.

### The profiles

DRALL<sup>+</sup> is available for the following screwhead profiles:

- ⊖ Slotted
- ⊕ PH cross-head
- ⊕ PZ cross-head
- ⊗ TORX®
- ⊗ TORX® Tamper Resistant with a central bore
- ⦿ Hex with a ball-end
- ⊕ TORQ-SET®

### The hand-stop helps stop injuries

Flange-like design. Supports your hand in the direction of the blade to prevent it slipping off the handle. Features integrated anti-roll shape.

### Tips

Black, extremely tough, retain their shape. Whether you use the straight-bladed or Phillips type – the crosshatched blade tips will accurately transmit maximum force to the screw head.

### Impact-resistant cap

For use under extreme conditions, the DRALL<sup>+</sup> is also available with a one-piece shaft, an impact head and a metal impact cap.



A new challenge every day, a new tool every day to meet that challenge. The new DRALL<sup>+</sup> series was developed for professionals faced with new challenges on a daily basis. Development focussed on three crucial user requirements: durability and reliability, safety in use, pleasant to handle. These requirements are met in full by DRALL<sup>+</sup> screwdrivers – in fact, they feel so natural, you will hardly notice them.

### The elastic handle components

The soft rubber textured thermoplastic elastomer (TPE) fits snugly in the hand. These sections are injection moulded around the hard core and bonded to it inseparably.

### The firm handle components

The green zones are made of high-grade, impact-safe polypropylene (PP). The tang is anchored in the core to allow force to be transferred through it.



### The multifunctional section

The lower end of the handle is deliberately made extra-long. This enables the thumb and index finger to wrap around more easily and spin the screwdriver.

### The transmission zone

The rounded cross-section in the central area combines maximum grip and easy turning.




### VDE insulated Screwdrivers

High-grade materials and durability testing guarantee absolute safety when working on AC systems up to 1000 V (effective voltage) or 1500 V DC.



## TCS 4650



175 x 350 x 35 mm, 8 pieces


Code	g
<b>96838767</b>	350

**No 4650** sizes T8; T9; T10; T15; T20; T25; T27; T30

## 4620

### ⊖ Screwdrivers for slotted screws DRALL<sup>+</sup>

DIN ISO 2380-1, -2, DIN 5264, ISO 2380-1, -2, Chrome Alloy Steel, chrome plated, black tips.



Code	size	a mm	b mm	L <sub>1</sub> mm	L <sub>2</sub> mm	g	
<b>4620 1035</b>	1	0.6	3.5	75	180	37	10
<b>4620 1040</b>	2	0.8	4.0	100	205	40	10
<b>4620 1055</b>	3	1.0	5.5	125	240	79	10
<b>4620 1065</b>	4	1.2	6.5	150	265	100	10
<b>4620 1080</b>	5	1.6	8.0	175	300	136	10
<b>4620 1100</b>	6	1.6	10.0	200	325	163	5
<b>4620 1120</b>	7	2.0	12.0	250	375	215	5

## 4621

### ⊖ Screwdrivers for slotted screws DRALL<sup>+</sup>

parallel blades, as per VSM (Swiss Standard), Chrome Alloy Steel, chrome plated, black tips.



Code	size	a mm	b mm	L <sub>1</sub> mm	L <sub>2</sub> mm	g	
<b>4621 1025</b>	0	0.4	2.5	80	185	36	10
<b>4621 1035</b>	1	0.5	3.5	90	195	40	10
<b>4621 1040</b>	2	0.6	4.0	100	205	42	10
<b>4621 1055</b>	3	0.8	5.5	120	235	78	10
<b>4621 1065</b>	4	1.0	6.5	140	255	96	10
<b>4621 1080</b>	5	1.2	8.0	160	275	117	10
<b>4621 1100</b>	6	1.6	10.0	180	305	160	10

## 4622

### ⊖ Screwdrivers for slotted screws DRALL<sup>+</sup>

DIN ISO 2380-1, -2, DIN 5264, ISO 2380-1, -2, with hexagon, Chrome Alloy Steel, chrome plated, black tips.



Code	size	a mm	b mm	L <sub>1</sub> mm	L <sub>2</sub> mm	g	
<b>4622 1055</b>	1	1.0	5.5	100	215	85	10
<b>4622 1065</b>	2	1.2	6.5	125	240	100	10
<b>4622 1080</b>	3	1.2	8.0	150	275	159	10
<b>4622 1100</b>	4	1.6	10.0	175	300	174	10
<b>4622 1120</b>	5	2.0	12.0	200	325	310	5
<b>4622 1140</b>	6	2.5	14.0	250	375	331	5

## 4622SK

### ⊖ Screwdrivers for slotted screws DRALL<sup>+</sup>

DIN ISO 2380-1, -2, DIN 5264, ISO 2380-1, -2, with impact cap and hexagonal shank, Chrome Alloy Steel, chrome plated, black tips.



Code	size	a mm	b mm	L <sub>1</sub> mm	L <sub>2</sub> mm	g	
<b>46220040</b>	1	0.8	4.0	90	195	50	10
<b>46220055</b>	2	1.0	5.5	100	215	106	10
<b>46220065</b>	3	1.2	6.5	125	240	135	5
<b>46220080</b>	4	1.2	8.0	150	275	191	5
<b>46220100</b>	5	1.6	10.0	175	300	226	5
<b>46220120</b>	6	2.0	12.0	200	325	267	5
<b>46220140</b>	7	2.5	14.0	250	375	340	5

## 4724

### ⊖ Carburettor screwdrivers DRALL

DIN ISO 2380-1, -2, DIN 5264, ISO 2380-1, -2, stubby, Chrome Alloy Steel, chrome plated, black tips.




Code	size	a mm	b mm	L <sub>1</sub> mm	L <sub>2</sub> mm	g	
<b>4724 1045</b>	1	0.6	3.5	25	80	34	10
<b>4724 1060</b>	2	1.0	5.5	25	80	32	10
<b>4724 1080</b>	3	1.2	8.0	25	80	39	10

## 4628

### ⊖ Electricians screwdrivers for slotted screws DRALL<sup>+</sup>

DIN ISO 2380-1, -2, DIN 5264, ISO 2380-1, -2, Chrome Alloy Steel, chrome plated, black tips.



Code	size	a mm	b mm	L <sub>1</sub> mm	L <sub>2</sub> mm	g	
<b>4628 1025</b>	1	0.4	2.5	60	165	38	10
<b>4628 1035</b>	2	0.6	3.5	75	180	40	10
<b>4628 2035</b>	3	0.6	3.5	100	205	41	10
<b>4628 1040</b>	4	0.8	4.0	125	230	46	10
<b>4628 1055</b>	5	1.0	5.5	150	265	92	10
<b>4628 2055</b>	6	1.0	5.5	200	315	102	10

## 4630

### ⊕ Cross-head screwdrivers DRALL<sup>+</sup>

Phillips-Recess®, DIN ISO 8764-1, -2, ISO 8764-1, -2, Chrome Alloy Steel, chrome plated, black tips.



Code	PH size	L <sub>1</sub> mm	L <sub>2</sub> mm	g	
<b>4630 1000</b>	0	60	165	35	10
<b>4630 1001</b>	1	80	185	44	10
<b>4630 1002</b>	2	100	215	90	10
<b>4630 1003</b>	3	150	275	146	10

## 3K DRALL Screwdrivers

### 4891 3K DRALL set of screwdrivers

Set of 6 3K DRALL screwdrivers.

Content:

- ⊖ 4820: 0.6 x 3.5 x 75 mm  
0.8 x 4.0 x 100 mm  
1.0 x 5.5 x 125 mm  
1.2 x 6.5 x 150 mm
- ⊕ 4830: size 1; size 2



Code	g	g
96489110	530	1

### 4892 3K DRALL set of screwdrivers

Set of 8 3K DRALL screwdrivers.

Content:

- ⊖ 4820: 0.6 x 3.5 x 75 mm  
0.8 x 4.0 x 100 mm  
1.0 x 5.5 x 125 mm  
1.2 x 6.5 x 150 mm  
1.6 x 8.0 x 175 mm
- ⊕ 4830: size 1; size 2; size 3



Code	g	g
96489210	745	1

### 4899 3K DRALL set of TORX® screwdrivers

Set of 9 3K DRALL screwdrivers for TORX® screws (TORX® TAMPER RESISTANT).

Content:

- ⊕ 4856: T8; T9; T10; T15; T20; T25; T27; T30; T40 (with hollow point)



Code	g	g
96489910	513	1

### TCS 4820/4830



175 x 350 x 35 mm, 7 pieces

Code	g
96838184	555

No 4820	0.6 x 3.5 x 75 mm; 0.8 x 4.0 x 100 mm; 1.0 x 5.5 x 125 mm; 1.2 x 6.5 x 150 mm
---------	--

No 4830	sizes 1; 2; 3
---------	---------------

### TCS 4724/4840+10767



530 x 350 x 45 mm, 24 pieces

Code	g
96830706	1755

No 4628	size 1 (0.4 x 2.5 x 60 mm)
---------	----------------------------

No 4724	size 2 (1.0 x 5.5 x 25 mm)
---------	----------------------------

No 4734	size 2
No 4744	size 1

No 4820	0.6 x 3.5 x 75 mm; 0.8 x 4.0 x 100 mm; 1.2 x 6.5 x 150 mm; 1.6 x 10.0 x 200 mm; 2.0 x 12.0 x 250 mm
---------	---

No 4830	sizes 1; 2; 3
No 4840	size 1

No 10767/9	sizes 1.5; 2; 2.5; 3; 4; 5; 6; 8; 10 mm
------------	---

No 7756	
---------	--

No 12922E	
-----------	--

### 4820 3K DRALL screwdrivers for slotted screws

DIN 5265, ISO 2380, Chrome Alloy Steel, matt chrome plated, black tips.



Code	a mm	b mm	L <sub>1</sub> mm	L <sub>2</sub> mm	g	g
48201035	0.6	3.5	75	170	23	10
48201040	0.8	4.0	100	195	32	10
48202055	1.0	5.5	125	220	58	10
48201065	1.2	6.5	150	265	100	10
48201080	1.6	8.0	175	290	118	10
48201100	1.6	10.0	200	315	158	5
48202100	2.0	12.0	250	375	218	5

### 4830 3K DRALL cross-head screwdrivers

Phillips-Recess®, DIN 5262, ISO 8764, Chrome Alloy Steel, matt chrome plated, black tips.



Code	PH size	L <sub>1</sub> mm	L <sub>2</sub> mm	g	g
48301000	0	60	155	28	10
48301001	1	80	175	33	10
48301002	2	100	215	70	10
48301003	3	150	275	126	5
48301004	4	200	325	251	5

**4840**

**3K DRALL cross-head screwdrivers**

POZIDRIV/SUPADRIV®,  
DIN 5262, ISO 8764,  
Chrome Alloy Steel,  
matt chrome plated, black tips.



Code	PZ size	L <sub>1</sub> mm	L <sub>2</sub> mm	△△ g	
<b>4840 1001</b>	<b>1</b>	80	175	33	10
<b>4840 1002</b>	<b>2</b>	100	215	70	10

**TCS 4856**



175 x 350 x 40 mm, 7 pieces

Code	△△ g
<b>9683 87 55</b>	447

**No 4856** sizes T8; T9; T10; T15; T20; T25; T30

**4856**

**3K DRALL TORX® screwdrivers**

with hollow point  
(TORX® TAMPER RESISTANT),  
Chrome Alloy Steel,  
matt chrome plated, black tips.



Code	size	mm	L <sub>1</sub> mm	L <sub>2</sub> mm	△△ g	
<b>4856 0006</b>	<b>T6*</b>	1.6	50	145	45	5
<b>4856 0007</b>	<b>T7</b>	2.0	50	145	37	5
<b>4856 0008</b>	<b>T8</b>	2.3	60	155	50	5
<b>4856 0009</b>	<b>T9</b>	2.5	60	155	50	5
<b>4856 0010</b>	<b>T10</b>	2.7	80	175	26	5
<b>4856 0015</b>	<b>T15</b>	3.3	80	175	52	5
<b>4856 0020</b>	<b>T20</b>	3.8	100	215	32	5
<b>4856 0025</b>	<b>T25</b>	4.4	100	215	55	5
<b>4856 0027</b>	<b>T27</b>	5.0	115	230	58	5
<b>4856 0030</b>	<b>T30</b>	5.5	115	230	63	5
<b>4856 0040</b>	<b>T40</b>	6.6	115	240	86	5

\* without hollow point



**Electronics Screwdrivers**

**4797**

**Electronics screwdrivers set**

7 pieces  
Content:

- ⊖ 4751: size 4 (0.3 x 1.5 x 40 mm)  
size 6 (0.4 x 2.0 x 60 mm)  
size 7 (0.4 x 2.5 x 75 mm)  
size 8 (0.5 x 3.0 x 75 mm)
- ⊕ 4752: size 00, size 0, size 1



Code	△△ g	
<b>9647 97 10</b>	285	1

**4751**

**⊖ Screwdrivers for slotted screws**



Code	size	a mm	b mm	L <sub>1</sub> mm	L <sub>2</sub> mm	△△ g	
<b>4751 0001</b>	<b>1</b>	0.16	0.8	40	140	12	5
<b>4751 0002</b>	<b>2</b>	0.18	1.0	40	140	12	5
<b>4751 0003</b>	<b>3</b>	0.25	1.2	40	140	12	5
<b>4751 0004</b>	<b>4</b>	0.3	1.5	40	140	19	5
<b>4751 0005</b>	<b>5</b>	0.3	1.8	60	160	10	5
<b>4751 0006</b>	<b>6</b>	0.4	2.0	60	160	19	5
<b>4751 0007</b>	<b>7</b>	0.4	2.5	75	175	14	5
<b>4751 0008</b>	<b>8</b>	0.5	3.0	75	175	16	5

**4752**

**⊕ Cross-head screwdrivers**

Phillips-Recess®.



Code	size	L <sub>1</sub> mm	L <sub>2</sub> mm	⊕ M	americ. No.	∅ mm	△△ g	
<b>4752 0010</b>	<b>00</b>	40	140	-	-	2.5	19	5
<b>4752 0020</b>	<b>0</b>	60	160	-2	0-1	3	13	5
<b>4752 0001</b>	<b>1</b>	80	180	2-3	2-4	4.5	24	5

**4753**

**● Hexagon socket screwdrivers**



Code	∅ mm/"	L <sub>1</sub> mm	L <sub>2</sub> mm	△△ g	
<b>4753 0007</b>	<b>0.7 / 0.028</b>	40	140	14	5
<b>4753 0009</b>	<b>0.9 / 0.035</b>	40	140	14	5
<b>4753 0013</b>	<b>1.3 / 0.050</b>	40	140	19	5
<b>4753 0015</b>	<b>1.5</b>	50	150	18	5

## 10760CV R/8

### Hexagon key wrenches

on ring, for socket head screws,  
Chrome Vanadium, nickel-plated.



Code	g	g	g
<b>9643 1521</b>	260	1	

Content: 2; 2.5; 3; 4; 5; 6; 8; 10 mm

### Hexagon key wrenches

in holder, DIN ISO 2936 (metric),  
for socket head screws,  
Chrome Vanadium, nickel-plated.



Code	No	g	g
<b>9643 1501</b>	<b>10760CV/9<sup>1)</sup></b>	245	1
<b>9643 5501</b>	<b>10760aCV/10Pc<sup>2)</sup></b>	269	1
<b>9643 5502</b>	<b>10760aCV/13<sup>3)</sup></b>	124	1

<sup>1)</sup> Content: 1.5; 2; 2.5; 3; 4; 5; 6; 8; 10 mm


<sup>2)</sup> Content: 1/16; 5/64; 3/32; 1/8; 5/32; 3/16; 7/32; 1/4; 5/16; 3/8" (in plastic-wallet)

<sup>3)</sup> Content (in two holders): 0.028; 0.035; 0.050; 1/16; 5/64; 3/32; 7/64; 1/8; 9/64; 5/32; 3/16; 7/32; 1/4"

## 10760CV

### Hexagon key wrenches

DIN ISO 2936 (metric), for socket head screws,  
Chrome Vanadium, nickel-plated (sizes 0.7; 0.9; 1.3 mm gunmetal finish).



Code	mm/"	L <sub>1</sub> mm	L <sub>2</sub> mm	g	g
<b>43 1500 70</b>	<b>0.7/0.028</b>	8	32	1	10
<b>43 1500 90</b>	<b>0.9/0.035</b>	10	32	1	10
<b>43 1501 30</b>	<b>1.3/0.050</b>	12	40	1	10
<b>43 1501 50</b>	<b>1.5</b>	14	45	1	10
<b>43 1500 02</b>	<b>2</b>	16	50	2	10
<b>43 1502 50</b>	<b>2.5</b>	18	56	3	10
<b>43 1500 03</b>	<b>3</b>	20	63	4	10
<b>43 1503 50</b>	<b>3.5</b>	22	66	7	10
<b>43 1500 04</b>	<b>4</b>	25	70	10	10
<b>43 1500 05</b>	<b>5</b>	28	80	18	10
<b>43 1500 06</b>	<b>6</b>	32	90	29	10
<b>43 1500 07</b>	<b>7</b>	34	95	42	10
<b>43 1500 08</b>	<b>8</b>	36	100	59	10
<b>43 1500 09</b>	<b>9</b>	38	105	80	10
<b>43 1500 10</b>	<b>10</b>	40	112	103	10
<b>43 1500 11</b>	<b>11</b>	42	119	130	10
<b>43 1500 12</b>	<b>12</b>	45	125	169	5
<b>43 1500 14</b>	<b>14</b>	56	140	261	5
<b>43 1500 17</b>	<b>17</b>	63	160	442	5
<b>43 1500 19</b>	<b>19</b>	70	180	603	5
<b>43 1500 22</b>	<b>22</b>	80	200	938	1
<b>43 1500 24</b>	<b>24</b>	90	224	1248	1
<b>43 1500 27</b>	<b>27</b>	100	250	1692	1
<b>43 1500 30</b>	<b>30</b>	112	280	2434	1
<b>43 1500 32</b>	<b>32</b>	125	315	3117	1
<b>43 1500 36</b>	<b>36</b>	140	355	4430	1

## 10760aCV

### Hexagon key wrenches

Code	mm/"	L <sub>1</sub> mm	L <sub>2</sub> mm	g	g
<b>43 1500 70</b>	<b>0.7/0.028</b>	8	32	1	10
<b>43 1500 90</b>	<b>0.9/0.035</b>	10	32	1	10
<b>43 1501 30</b>	<b>1.3/0.050</b>	12	40	1	10
<b>43 5500 03</b>	<b>3/64</b>	14	45	1	10
<b>43 5500 04</b>	<b>1/16</b>	15	45	1	10
<b>43 5500 05</b>	<b>5/64</b>	16	50	2	10
<b>43 5500 06</b>	<b>3/32</b>	17	51	3	10
<b>43 5500 07</b>	<b>7/64</b>	20	54	4	10
<b>43 5500 08</b>	<b>1/8</b>	22	57	5	10
<b>43 5500 09</b>	<b>9/64</b>	23	63	7	10
<b>43 5500 10</b>	<b>5/32</b>	25	65	10	10
<b>43 5500 12</b>	<b>3/16</b>	29	70	15	10
<b>43 5500 14</b>	<b>7/32</b>	32	80	23	10
<b>43 5500 16</b>	<b>1/4</b>	32	87	32	10
<b>43 5500 18</b>	<b>9/32</b>	35	95	45	10
<b>43 5500 20</b>	<b>5/16</b>	40	98	59	10
<b>43 5500 22</b>	<b>11/32</b>	41	105	75	10
<b>43 5500 24</b>	<b>3/8</b>	45	110	95	10
<b>43 5500 28</b>	<b>7/16</b>	48	124	143	10
<b>43 5500 32</b>	<b>1/2</b>	50	133	200	5
<b>43 5500 34</b>	<b>9/16</b>	57	152	380	5
<b>43 5500 36</b>	<b>5/8</b>	59	160	380	5
<b>43 5500 40</b>	<b>3/4</b>	70	180	605	5
<b>43 5500 44</b>	<b>7/8</b>	80	200	945	1

